

LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
NUMMER 829 033				E		Contact pin base material change from CuSn (Phosphor bronze) to CuZn (Brass). Plating change from MIN. 0.8µm gold plating to min. 0.7µm Pd Ni + 0.1µm gold flash at contact area (Area F).	18JUL2014	TJ	JK
VERWENDET FÜR									
WAR NR. E-87-9102									

POLZ. PRO REIHE	L±0.5	BESTELL-NR.
—	—	—
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	829 033 -7
8	20.32	-8
9	22.86	-9
10	25.40	-0
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2-
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5- 829 033 -0

STECKSEITE: IM BEREICH "F" 0.7µm PdNi + 0.1µm GOLD FLASH ÜBER 1.27 µm Ni

LÖTSEITE: MIN. 2.5 µm ZINN ÜBER 1.27 µm Ni

OBSELETE PARTS: OBSELETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CAD-ORIGINAL		
ZEICHNUNG NICHT ÄNDERN		
KONTAKTSTIFT	CuZn	1
STIFTGEHÄUSE	PBTP-GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

DIMENSIONS:		DWN	12.03.87	MATERIAL	SEE TABLE	FINISH	SEE TABLE
mm		AUGUSTINIAK					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 19.03.87					
±0.2 mm		M.Schaarschmidt					
± -		APVD -					
PRODUCT SPEC		108-18012					
APPLICATION SPEC		-					
WEIGHT		-					
CUSTOMER DRAWING							

TE Connectivity	
SPEZ. AMPMODU II STIFTELEISTE ZWEIREIHIG	
SIZE	A4
CAGE CODE	00779
DRAWING NO	C-829033
RESTRICTED TO	-

SCALE		SHEET		REV	
4:1		1 OF 1		E	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-829033-0](#)