


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	CHANGES PER ECO-17-001274	10MAY2017	LA	GF



1. ASSEMBLY TO BE 100% TESTED FOR CONTINUITY, SHORTS, AND OPENS, CABLES ASSEMBLYS ARE ALSO TO BE 100% TESTED FOR SIGNAL INTEGRITY, TO SAS 3.0 REQUIREMENTS.

2. ROHS AND REACH COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE SPECIFICATION TEC-138-702.


3. LABEL CENTERED AND LABEL INFORMATION AS BELOW:

2820330-[]	TE LOGO AND P/N
----- METERS	LENGTH
MADE IN -----	COUNTRY OF ORIGIN
YYWWSSSS	YYWW IS DATE CODE, SSSS IS SERIAL
	BAR FOR YYWWSSSS

4. SEE SHEET #2 FOR WIRING SCHEMATIC.

1000 $\begin{smallmatrix} +25 \\ -0 \end{smallmatrix}$	2820330-4
700 $\begin{smallmatrix} +25 \\ -0 \end{smallmatrix}$	2820330-3
500 $\begin{smallmatrix} +25 \\ -0 \end{smallmatrix}$	2820330-2
300 $\begin{smallmatrix} +25 \\ -0 \end{smallmatrix}$	2820330-1
"L"[MM]	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.YI 16/JUN/2014	TE Connectivity	
DIMENSIONS: mm		CHK G.GUTGOLD 16/JUN/2014		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.GUTGOLD 16/JUN/2014	NAME C/A, INTERNAL HD MINI SAS, STR TO R/A 85 OHMS, 4X	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC	SIZE A2	
MATERIAL -		WEIGHT 0	CAGE CODE 00779	DRAWING NO C=2820330
FINISH -		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE N.T.S.	SHEET 1 OF 2	REV B



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.YI 16/JUN/2014 CHK G.GUTGOLD 16/JUN/2014 APVD G.GUTGOLD 16/JUN/2014 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		 TE Connectivity C/A, INTERNAL HD MINI SAS, STR TO R/A 85 OHMS, 4X, HALOGENATED —							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME							
		FINISH —		SIZE A2		CAGE CODE 00779		DRAWING NO C=2820330		RESTRICTED TO —	
MATERIAL —		CUSTOMER DRAWING		SCALE N.T.S.		SHEET 2 of 2		REV B			

2820330

1

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2820330-2](#)