




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECO-17-007675	07APR2017	GL	CP
	B	FIX INTEL REV	06JUN2017	GL	CP




2821719-2, -4

 WRAP (SHEET 1)	104.5±5	460±5	-	2821719-4 
 FLAG (SHEET 2)	75±5	142±5	-	2821719-3
 WRAP (SHEET 1)	104.5±5	405±5	H98342-004	2821719-2
 FLAG (SHEET 2)	104.5±5	208±5	H98340-004	2821719-1
LABEL TYPE	M	L	INTEL PART NO	TE PART NO

1	1	1	1	PULL TAB.	12
-	1	-	1	LABEL, FLAG	11
AR	AR	AR	AR	ACETATE TAPE, BLACK	10
1	-	1	-	LABEL, WRAP AROUND	9
AR	AR	AR	AR	SLEEVEING, EXPANDABLE	8
AR	AR	AR	AR	85 OHM TWINAX CABLE, 30AWG 25G TURBO TWIN™ 	7
1	1	1	1	OVERMOLDED STRAIN RELIEF, LECA	6
2	2	2	2	OVERMOLDED STRAIN RELIEF, IFP	5
1	1	1	1	DUST COVER, LECA (NOT SHOWN)	4
2	2	2	2	DUST COVER, IFP (NOT SHOWN)	3
1	1	1	1	LEC 54A RECPT, 54 POSN.	2
2	2	2	2	IFP PLUG, 28 POSN,	1
-4	-3	-2	-1	DESCRIPTION	ITEM NO



CABLE PINOUT				
PAIR	PIN NAME	P1	P2	P3
GROUND BUS	-	1	-	1
1	HF10_RX_DN(1)	2	-	2
	HF10_RX_DP(1)	3	-	3
GROUND BUS	-	4	-	4
2	HF10_RX_DN(3)	5	-	5
	HF10_RX_DP(3)	6	-	6
GROUND BUS	-	7	1	7
3	HF11_RX_DN(1)	-	2	8
	HF11_RX_DP(1)	-	3	9
GROUND BUS	-	-	4	10
4	HF11_RX_DN(3)	-	5	11
	HF11_RX_DP(3)	-	6	12
GROUND BUS	-	-	7	13
GROUND BUS	-	-	-	14
GROUND BUS	-	8	-	15
5	HF10_TX_DP(4)	9	-	16
	HF10_TX_DN(4)	10	-	17
GROUND BUS	-	11	-	18
6	HF10_TX_DP(2)	12	-	19
	HF10_TX_DN(2)	13	-	20
GROUND BUS	-	14	8	21
7	HF11_TX_DP(4)	-	9	22
	HF11_TX_DN(4)	-	10	23
GROUND BUS	-	-	11	24
8	HF11_TX_DP(2)	-	12	25
	HF11_TX_DN(2)	-	13	26
GROUND BUS	-	-	14	27
GROUND BUS	-	-	15	28
9	HF11_TX_DN(1)	-	16	29
	HF11_TX_DP(1)	-	17	30
GROUND BUS	-	-	18	31
10	HF11_TX_DN(3)	-	19	32
	HF11_TX_DP(3)	-	20	33
GROUND BUS	-	15	21	34
11	HF10_TX_DN(1)	16	-	35
	HF10_TX_DP(1)	17	-	36
GROUND BUS	-	18	-	37
12	HF10_TX_DN(3)	19	-	38
	HF10_TX_DP(3)	20	-	39
GROUND BUS	-	21	-	40
GROUND BUS	-	-	-	41
GROUND BUS	-	-	22	42
13	HF11_RX_DP(4)	-	23	43
	HF11_RX_DN(4)	-	24	44
GROUND BUS	-	-	25	45
14	HF11_RX_DP(2)	-	26	46
	HF11_RX_DN(2)	-	27	47
GROUND BUS	-	22	28	48
15	HF10_RX_DP(4)	23	-	49
	HF10_RX_DN(4)	24	-	50
GROUND BUS	-	25	-	51
16	HF10_RX_DP(2)	26	-	52
	HF10_RX_DN(2)	27	-	53
GROUND BUS	-	28	-	54




2821719-1, -3
FLAG LABEL
REQUIREMENT
ALL ASSEMBLY REQUIREMENTS
SAME AS -2 EXCEPT FOR
LABEL


REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-

1. THIS ASSEMBLY CONFORMS TO INTEL PART NO. (SEE TABLE).
2. EACH ASSEMBLY TESTED FOR OPENS, SHORTS AND SIGNAL INTEGRITY.
3. ROHS AND REACH COMPLIANCE: PRODUCT AND PROCESSING MEETS THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
4. EACH ASSEMBLY PACKAGED IN AN ANTISTATIC BAG.


5 LABEL INFORMATION (ITEM 9): 2821719-2




6 LABEL INFORMATION (ITEM 11): 2821719-3



7 LABEL INFORMATION (ITEM 9): 2821719-4



8 LABEL INFORMATION (ITEM 11): 2821719-1



9. CABLE ASSEMBLY BUILT IN ACCORDANCE WITH INTEL DESIGN GUIDE 1.0

10 FINISH (CONTACT PADS): 30μIN MINIMUM GOLD PER TE SPEC 112-162-1 OVER 100μIN MINIMUM NICKEL PER TE SPEC 112-25-2.

11 FINISH: 50μIN MINIMUM GOLD PER TE SPEC 112-162-5, IN LOCALIZED GOLD PLATE AREA, OVER 50μIN MINIMUM NICKEL PER TE SPEC 112-25-2 ON ENTIRE STOCK.

12 CABLE PART #: 023B2LF023
CABLE SPEC: 104-1587

13 CABLE ASSEMBLY LENGTH OFFERED BY TE IS NOT REFERENCED WITHIN INTEL DESIGN GUIDE 1.0

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN T. SMITH CHK C. POGASH APVD	08JUN2016 08JUN2016 -	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±" 1 PLC ±" 2 PLC ±" 3 PLC ±" 4 PLC ±" ANGLES ±" FINISH		PRODUCT SPEC APPLICATION SPEC	NAME IFP ASSEMBLY, TYPE A, STRAIGHT EXIT 2-PORT, NON-INVERTED.
MATERIAL - -	- -	WEIGHT -	SIZE A1	CAGE CODE -	DRAWING NO. C=2821719
CUSTOMER DRAWING				SCALE 1:1	SHEET 2 OF 2 REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2821719-1](#)