

4



3

2

1

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	PLATING CHANGE TO PdNi + Au FLASH AT AREA F	19MAY2014	KJK	JK

POS. PER ROW "n"	L±0.4	PART NO.
2	4.58	829 538 -2
3	7.12	829 538 -3
4	9.66	829 538 -4
5	12.20	829 538 -5
6	14.74	829 538 -6
7	17.28	829 538 -7
8	19.82	829 538 -8
15	37.60	1- 829 538 -5



NOTES:

- 1 MATING SIDE AT AREA "F"
MIN. 0.7µm PdNi + 0.1µm GOLD FLASH
OVER 1.27µm NICKEL
SOLDER SIDE: MIN. 3.0µm TIN OVER 1.27µm NICKEL

2	CONTACT PIN KONTAKTSTIFT	CuZn	1
1	PIN HOUSING STIFTGEHÄUSE	PA 4/6	BLACK SCHWARZ
POS.	BENENNUNG EINZELTEIL	WERKSTOFF	OBERFLÄCHE
[ITEM NO.]	[DESCRIPTION]	[MATERIAL]	FARBE
			[FINISH]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.2mm

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH
SEE TABLE

DWN
MULLER
09.02.90

CHK
SCHAARSCHMIDT
12.02.90

APVD
—

PRODUCT SPEC
108-18012

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

NAME
AMPMODU II PIN HEADER, DUAL ROW

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-829538

RESTRICTED TO
—

SCALE
4:1

SHEET
1 OF 1

REV
F

1470-19 (3/11)

19MAY2014

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[829538-4](#)