


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	PLATING CHANGED TO TRIBOR	10JAN2017	RP	PS

POS.	L±0.4	PART NUMBER
2	5.08	
3	7.62	
4	10.16	5-966443-4
5	12.70	
6	15.24	5-966443-6
7	17.78	
8	20.32	
9	22.86	
10	25.40	6-966443-0
11	27.94	
12	30.48	
13	33.02	
14	35.56	
15	38.10	
16	40.64	
17	43.18	
18	45.72	
19	48.26	
20	50.80	
21	53.34	
22	55.88	
23	58.42	
24	60.96	
25	63.50	
26	66.04	
27	68.58	
28	71.12	
29	73.66	
30	76.20	
31	78.74	
32	81.28	
33	83.82	
34	86.36	
35	88.90	
36	91.44	
37	93.98	
38	96.52	
39	99.06	
40	101.60	
41	104.14	
42	106.68	
43	109.22	
44	111.76	
45	114.30	
46	116.84	
47	119.38	
48	121.92	
49	124.46	
50	127.00	9-966443-9



2	CONTACT PIN	CuSn	△
1	PIN HOUSING	PBT	GREEN
ITEM	DESCRIPTION	MATERIAL	SURFACE/COLOUR

REMARKS:

△ FINISH: TRIBOR®
UNDERLAYER: 2-4μm Ni-P(NICKEL-PHOSPHOROUS)
CONTACT AREA: 0.12-0.27μm Au(GOLD) BY AREA "F"
SOLDER TYNES: 3-5μm Sn(MATTE TIN)


2. PERMEABILITY $\mu_R \leq 1.0005$

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN
± 0.2mm

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES / WINKEL	± -



DWN 17.02.94
F.RIECHARDT

CHK 17.02.94
M.SCHAARSCHMIDT

APVD -

PRODUCT SPEC
PRODUKTSPEZ.

APPLICATION SPEC

-

WEIGHT
GEWICHT

MATERIAL

-

FINISH
OBERFLAECHE/FARBE

-



TE Connectivity

NAME

AMPMODU II, PIN HEADER
SINGLE ROW, NON MAGNETIC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-966443

-

CUSTOMER DRAWING

SCALE

1:1

SHEET
BLATT

1

OF

1

REV

B

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

VERWENDET FÜR

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG.

By -

COPYRIGHT -

©

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-966443-9](#)