






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	15AUG2017	WH	DZ



- 1 WIRE RANGE 0.3-0.82mm² [22-18 AWG]
- 2 INSULATION RANGE: DIA 1.50-3.10 mm [.060-.122 in]
- 3 FINISH: 2.54μm [.0001 in] MINIMUM PRE-TIN ALL OVER.
- 4 MATING PART: 2825210-1(STRIP TYPE) OR 2825212-1(LOOSE TYPE)



PRE-TIN 	HIGH PERFORMANCE COPPER ALLOY	2825213-1
FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WARREN HUO 15AUG2017		 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK DANIEL ZHANG 15AUG2017							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DANIEL ZHANG 15AUG2017		NAME SOCKET TERMINAL, VAL-U-LOK HCS, LOOSE PIECE -				
	0 PLC ± - 1 PLC ± 0.25 [.010] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-150000						
	FINISH		APPLICATION SPEC 114-13172		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	MATERIAL SEE TABLE	SEE TABLE		WEIGHT 0	A2	00779	C=2825213	-	
CUSTOMER DRAWING				SCALE	N/A	SHEET	1 of 1	REV	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2825213-1](#)