

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	26AUG2019	RV	DH

## Ordering Information


SSC	01	2	A	A	A
Series SSC Discrete Industrial Timer	Output 2 = DPDT Relay				
Operating Mode 01 = On-Delay 02 = Off-Delay 03 = Interval					
Timing Range A = 0.1 to 3 sec. B = 0.5 to 15 sec. C = 1 to 30 sec. D = 2 to 60 sec. E = 4 to 120 sec. F = 6 to 180 sec. G = 10 to 300 sec. I = 2 to 60 min. K = 3 to 180 cycles L = 0.33 to 10 min. M = 0.5 to 15 min. N = 1 to 30 min. P = 0.1 to 10 min.					

Operating Voltage  
(+10%, -15%)



A = 120VAC, 50/60 Hz.  
/ 120VDC  
B = 240VAC, 50/60 Hz.  
E = 24VAC, 50/60 Hz. /  
24VDC  
F = 48VAC, 50/60 Hz. /  
48VDC  
Q = 12VDC (±10%)

## Timing Adjustment


A = Knob Adjust  
B = External Potentiometer  
or resistor (Operating  
modes 1 and 3 only).  
F = Fixed Times—Specify  
time delay in seconds  
per the following  
examples:  
F9.000 = 9 sec.  
F99.00 = 99 sec.  
F999.0 = 9999 sec.  
F1000 = 1000 sec.



Insulated, shielded two-conductor  
cable similar to BELDEN 8719,  
8720 or 8769 required for leads  
longer than 6 inches. Max.  
permissible length is 50 feet.





Wiring Diagrams (Bottom Views)



## Outline Dimensions

ALL DIMENSIONS ARE IN INCHES(MM).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RV		26AUG2019		<div>TE Connectivity</div>					
		CHK RV		26AUG2019							
		APVD DH		26AUG2019		NAME					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC		SSC SERIES TIME DELAY RELAY					
				—		—					
				APPLICATION SPEC		—					
				—		—					
				WEIGHT —		—					
MATERIAL —		FINISH —		SIZE A3		CAGE CODE —		DRAWING NO C=SSC-SERIES		RESTRICTED T —	
CUSTOMER DRAWING						SCALE NTS		SHEET 1 OF 1		REV A	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSC22ABA](#)