




Issue de la norme EN4165
Arise of EN4165 standard

DMC-M 99-02 BX



X: Codage A,B,C,D,E,F,G,H ou N (universel)
X: Keying A,B,C,D,E,F,G,H or N (universal)
(1)

CARACTERISTIQUES:

Température d'utilisation: -55°C à +175°C

Matériaux: Thermoplastique, silicone fluoré

Tenue de tension:

- contacts #22 : 1300 V eff. ; 50Hz
- contacts #20 : 1500 V eff. ; 50Hz

Masse: 4,4g Maxi


Dimensions: Millimètres [pouces]

Utilisation de Contacts:

- 8 contacts femelles #22 - EN3155-003F2222
- 3 contacts femelles #20 - EN3155-003F2020

Outils insertion/extraction:

- #22 - M81969/14-01
- #20 - M15570-20



CHARACTERISTICS:

Operating temperature range: -55°C to +175°C

Material: Thermoplastic and fluorosilicone

Withstanding voltage:

- contacts #22 : 1300 V eff. ; 50Hz
- contacts #20 : 1500 V eff. ; 50Hz

Weight: 4,4g Maxi


Dimensions: Millimeters [inches]

Use of contacts:

- 8 Socket #22 - EN3155-003F2222
- 3 Socket #20 - EN3155-003F2020

Insertion/extraction tool fo contact:

- #22 - M81969/14-01
- #20 - M15570-20



Module livré sans contact / Module delivered without contact

c	10/04/2017	OE080417	SERIE DMC-M	DATE 21/11/2013	VISA Creation Created	VISA Approbation Approval		
b	13/02/2014	OE190214						
Revision	Date	Observations	DESIGNATION Module Femelle High-speed 99-02 <i>Female High-speed Module 99-02</i>	REF : DMC-M 99-02 BX P/N: (1)			-	-
ORIGINE : DE122/12							VERSION	REVISION
 Connecteurs Electriques Deutsch 17, rue LAVOISIER - BP 117 - 27091 EVREUX CEDEX 09 - FRANCE			FICHE TECHNIQUE <i>TECHNICAL DATA SHEET</i>				204-19-C/101	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ZPF000000000114887](#)