


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER 0G3B-0119-01	04JAN2002	EZ	DB
			CI	REVISED PER ECO-08-003244	06FEB2008	SS	CR




CLAMPING SCREW


1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2 WIRE SIZE RANGE:
12 - 30 AWG

3 NOT CUMULATIVE TOLERANCE.





284049-3 AS SHOWN



WIRE ENTRY

RETENTION LATCH



POLARIZATION KEY SLOT

MATING FACE

2.81 REF

7.62±0.08

3

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E. ZANOLINI 04JAN2002	Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK E. ZANOLINI 04JAN2002				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 04JAN2002	NAME TERMINAL BLOCK VERTICAL PLUG STACKING, RIGHT HAND 7.62mm PITCH			
0 PLC ±- 1 PLC ±.3 2 PLC ±.25 3 PLC ±- 4 PLC ±- ANGLES ±2		PRODUCT SPEC -	SIZE A3			
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779			
FINISH -		WEIGHT -	DRAWING NO C-284049			
CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 1		
				REV CI		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284049-3](#)