


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY ALL RIGHTS RESERVED

LOC	DIST	REVISIONS			
		P	LIR	DESCRIPTION	DATE
FB	00		A2	REVISED PER	ECR-16-012124
					07DEC16
					T.Q
					W.H



TYPE 1







TYPE 2

TOLERANCES UNLESS OTHERWISE SPECIFIED:


10> : ±0.2
30> * >10 : ±0.25
100> * >30 : ±0.3
ANGLE : ±3°

NOTE:
1. PEELING STRENGTH: 0.20-0.69N (20-70gf)
PEELING ANGLE: 165-180°
PEELING SPEED: 300mm/MINUTE.



		DWN S.XU	31JAN03			TE Connectivity					
		CHK S.YAO	31JAN03								
		APVD T.SASAKI	31JAN03	NAME							
		PRODUCT SPEC 108-60018		AMP Mini Common Terminated (CT) Connector 1.5mm PITCH							
		APPLICATION SPEC 114-5223		SINGLE ROW POST HDR ASS'Y (V) SMT TYPE							
		WEIGHT		WITH BOSS, POLYIMIDE TAPE, EMOSS TAPE PACKAGED							
DIMENSIONS: mm				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL				A3	00779	C-292232	-				
CUSTOMER DRAWING				SCALE	NON		SHEET	OF	4	REV	A2

LOC	DIST	REVISIONS							
FB	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
				SEE SHEET 1					



TYPE 2	49.5	45.5	5.0	9.5	40.4	29.9	44	32.9	20.2±0.15	500	20	BEIGE	2-292232-0
	49.5	45.5	5.0	9.5	40.4	28.4	44	31.4		500	19		1-292232-9
	49.5	45.5	5.0	9.5	40.4	26.9	44	29.9		500	18		1-292232-8
	49.5	45.5	5.0	9.5	40.4	25.4	44	28.4		500	17		1-292232-7
	49.5	45.5	5.0	9.5	40.4	23.9	44	26.9		500	16		1-292232-6
	49.5	45.5	5.0	9.5	40.4	22.4	44	25.4		500	15		1-292232-5
	49.5	45.5	5.0	9.5	40.4	20.9	44	23.9		500	14		1-292232-4
	49.5	45.5	5.0	9.5	40.4	19.4	44	22.4		500	13		1-292232-3
	37.5	33.5	5.0	9.5	28.4	17.9	32	20.9	14.2	500	12		1-292232-2
	37.5	33.5	5.0	9.5	28.4	16.4	32	19.4	14.2	500	11		1-292232-1
37.5	33.5	5.0	9.5	28.4	14.9	32	17.9	14.2	500	10	1-292232-0		
37.5	33.5	5.0	6.5	28.4	13.4	32	16.4	14.2	500	9	292232-9		
TYPE 1	29.5	25.5	5.0	6.5	-	11.9	24	14.9	11.5	500	8	292232-8	
	29.5	25.5	5.0	6.5	-	10.4	24	13.4	11.5	500	7	292232-7	
	29.5	25.5	5.0	6.5	-	8.9	24	11.9	11.5	500	6	292232-6	
	29.5	25.5	5.0	9.5	-	7.4	24	10.4	11.5	500	5	292232-5	
	21.5	17.5	5.0	8.0	-	5.9	16	8.9	7.5	500	4	292232-4	
	21.5	17.5	5.0	6.5	-	4.4	16	7.4	7.5	500	3	292232-3	
TAPE TYPE	W2	W1	G	F	E	D	C	B	A	QTY/REEL	POS	COLOR	ON TAPE P/N
DIMENSIONS													

DIMENSIONS: mm	DWN	MATERIAL	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	TE TE Connectivity	
0 PLC ±	APVD	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH	
1 PLC ±	PRODUCT SPEC	SINGLE ROW POST HDR ASS'Y (V) SMT TYPE	
2 PLC ±	SEE SHEET 1	WITH POLYIMIDE TAPE, WITH BOSS, EMOSS TAPE PACKAGED	
3 PLC ±	APPLICATION SPEC	SIZE	RESTRICTED TO
4 PLC ±	SEE SHEET 1	CAGE CODE	
ANGLES ±	WEIGHT	DRAWING NO	
	CUSTOMER DRAWING	A4 00779	G-292232
		SCALE	SHEET 2 OF 4
		NON	REV A2

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT — BY — ALL RIGHTS RESERVED.

LOC
FB

00

REVISIONS





DESCRIPTION

DALE




1571

APVU

SEE SHEET 1





CIRCUIT No. 1—



SHOWN AS WIHTOUT TAPE

NOTES:

NOTES:
1. MATERIAL:
HOUSING: GLASS FILLED, HIGH HEAT RESISTANT NYLON, UL94V-0, COLOR: BEIGE OR BLACK
POST: Sn-100% BRASS WIRE
△ TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE,
FLOAT OF SOLDER TIME FROM DATUM SURFACE IS 0.1mm MAX.

DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC + 3 PLC ± 4 PLC ± ANGLES ±		DWN		 TE Connectivity	
				CHK			
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		APVD		NAME AMP MINI COMMON TERMINATION (CT) CONNECTOR 1.5 mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS	
				PRODUCT SPEC			
CUSTOMER DRAWING		WEIGHT		APPLICATION SPEC		SIZE A3	
				CAGE CODE			
				DRAWING NO		RESTRICTED TO	
				00779		G-292232	
				SCALE		SHEET	
				NON		3 OF 4	
				REV		A2	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

BY

© COPYRIGHT

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1	-	-	-

0.98	31.5	32.5	30.6	28.5	20	2-292232-0
0.93	30.0	31.0	29.1	27.0	19	1-292232-9
0.89	28.5	29.5	27.6	25.5	18	1-292232-8
0.84	27.0	28.0	26.1	24.0	17	1-292232-7
0.80	25.5	26.5	24.6	22.5	16	1-292232-6
0.75	24.0	25.0	23.1	21.0	15	1-292232-5
0.71	22.5	23.5	21.6	19.5	14	1-292232-4
0.66	21.0	22.0	20.1	18.0	13	1-292232-3
0.62	19.5	20.5	18.6	16.5	12	1-292232-2
0.57	18.0	19.0	17.1	15.0	11	1-292232-1
0.52	16.5	17.5	15.6	13.5	10	1-292232-0
0.48	15.0	16.0	14.1	12.0	9	292232-9
0.43	13.5	14.5	12.6	10.5	8	292232-8
0.39	12.0	13.0	11.1	9.0	7	292232-7
0.34	10.5	11.5	9.6	7.5	6	292232-6
0.30	9.0	10.0	8.1	6.0	5	292232-5
0.25	7.5	8.5	6.6	4.5	4	292232-4
0.20	6.0	7.0	5.1	3.0	3	292232-3
WEIGHT (g)	D	C	B	A	Pos.	BEIGE (NAT)
	DIMENSIONS					P/N

DIMENSIONS: mm	DWN	MATERIAL SEE SHEET 1	FINISH SEE SHEET 1
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	 TE Connectivity	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD		
	PRODUCT SPEC	NAME AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5 mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS	
	APPLICATION SPEC	SIZE A4	CAGE CODE 00779
	WEIGHT	DRAWING NO G-292232	RESTRICTED TO
CUSTOMER DRAWING		SCALE NON	SHEET 4 OF 4
		REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-292232-7](#)