

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

T.E. PROPRIETARY AND CONFIDENTIAL

This drawing contains proprietary information that shall not be disclosed, duplicated nor used in whole or in part for any purpose other than to evaluate this drawing.

LOC

DIST

REVISIONS

| P | LTR | DESCRIPTION               | DATE   | DWN | APVD |
|---|-----|---------------------------|--------|-----|------|
|   | A   | REVISED PER E.O. C8206    | 110510 | -   | RB   |
|   | B   | UPDATED PER ECO-14-008850 | 140611 | CB  | EA   |
|   | C   | UPDATED PER ECO-16-000868 | 160126 | MJ  | EA   |

S TYP.

R1 TYP.

R2 TYP.

MASTER KEYWAY

W° REF.

X° REF.

Y° REF.

Z° REF.

4X P

4X PP

1471-9 (3/11)

.085 MAX.

INSERT PROTRUSION

1.240 MAX.

V

W

D THREAD

RED FULLY MATED INDICATOR BAND REF.

BLUE BAND REF.

EXAMPLE OF PART NUMBER

DTS 20 x xx - xx P/S x-xxxx

MODIFICATION

KEYING POSITION

N = NORMAL, A, B, C, D & E

CONTACT STYLE

P = PIN

A = LESS PIN

H = 1500 CYCLES - PIN

INSERT ARRANGEMENT

SHELL SIZE

CLASS F = NICKEL

G = NICKEL SPACE GRADE

T = TEFLON NICKEL

W = OLIVE DRAB CADMIUM

Z = ZINC NICKEL

SHELL STYLE

20 = SQUARE FLANGE RECEPTACLE

CONNECTOR SERIES

DEUTSCH MIL-DTL-38999 SERIES III

5. FOR AVAILABILITY CONSULT FACTORY. (C1)

4. FOR APPLICABLE KEYING DIAGRAM AND PANEL CUTOUT DIMENSIONS, SEE MIL-DTL-38999. FOR AVAILABLE INSERT ARRANGEMENTS, SEE MIL-STD-1560.

3. GENERAL SPECIFICATIONS: THIS CONNECTOR MEETS THE PERFORMANCE AND INTERMATEABILITY REQUIREMENTS OF MIL-DTL-38999, SERIES III.

2. MATERIAL / FINISH: SHELL - ALUMINUM ALLOY / PLATING PER EXAMPLE PART NUMBER DESCRIPTION.  
RESILIENT INSERTS - SILICONE ELASTOMER  
PLASTIC INSERTS - THERMOPLASTIC.  
CONTACTS - COPPER ALLOY / GOLD PLATED.

1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.  
THREAD CALLOUTS ARE METRIC.

NOTES:

| SIZE                  | KEYING DESIGNATION LETTER | W°  | X°  | Y°  | Z°  |
|-----------------------|---------------------------|-----|-----|-----|-----|
| 9                     | N                         | 105 | 140 | 215 | 265 |
|                       | A                         | 102 | 132 | 248 | 320 |
|                       | B                         | 80  | 118 | 230 | 312 |
|                       | C                         | 35  | 140 | 205 | 275 |
|                       | D                         | 64  | 155 | 234 | 304 |
|                       | E                         | 91  | 131 | 197 | 240 |
| 11, 13 AND 15         | N                         | 95  | 141 | 208 | 236 |
|                       | A                         | 113 | 156 | 182 | 292 |
|                       | B                         | 90  | 145 | 195 | 252 |
|                       | C                         | 53  | 156 | 220 | 255 |
|                       | D                         | 119 | 146 | 176 | 298 |
|                       | E                         | 51  | 141 | 184 | 242 |
| 17, 19, 21, 23 AND 25 | N                         | 80  | 142 | 196 | 293 |
|                       | A                         | 135 | 170 | 200 | 310 |
|                       | B                         | 49  | 169 | 200 | 244 |
|                       | C                         | 66  | 140 | 200 | 257 |
|                       | D                         | 62  | 145 | 180 | 280 |
|                       | E                         | 79  | 153 | 197 | 272 |

| PART NUMBER     | SIZE | D THREAD          | P+.004<br>-.002 | PP+.004<br>-.002 | R1    | R2    | S±.011 | V<br>MAX. | W<br>MAX. |
|-----------------|------|-------------------|-----------------|------------------|-------|-------|--------|-----------|-----------|
| DTS20x09-xxP/Sx | 09   | M12X1.0-6g 0.100R | .128            | .216             | .719  | .594  | .937   | .822      | .098      |
| DTS20x11-xxP/Sx | 11   | M15X1.0-6g 0.100R | .128            | .194             | .812  | .719  | 1.031  | .822      | .098      |
| DTS20x13-xxP/Sx | 13   | M18X1.0-6g 0.100R | .128            | .194             | .906  | .812  | 1.126  | .822      | .098      |
| DTS20x15-xxP/Sx | 15   | M22X1.0-6g 0.100R | .128            | .173             | .969  | .906  | 1.220  | .822      | .098      |
| DTS20x17-xxP/Sx | 17   | M25X1.0-6g 0.100R | .128            | .194             | 1.062 | .969  | 1.311  | .822      | .098      |
| DTS20x19-xxP/Sx | 19   | M28X1.0-6g 0.100R | .128            | .194             | 1.156 | 1.062 | 1.437  | .822      | .098      |
| DTS20x21-xxP/Sx | 21   | M31X1.0-6g 0.100R | .128            | .194             | 1.250 | 1.156 | 1.563  | .791      | .126      |
| DTS20x23-xxP/Sx | 23   | M34X1.0-6g 0.100R | .154            | .242             | 1.375 | 1.250 | 1.689  | .791      | .126      |
| DTS20x25-xxP/Sx | 25   | M37X1.0-6g 0.100R | .154            | .242             | 1.500 | 1.375 | 1.811  | .791      | .126      |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN E HAB ALAWNEH 070410

CHK JAMES FRIEDHOF 070523

APVD ALEX RENGIFO 110511

DIMENSIONS:  
INCH

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±-  
1 PLC ±0.1  
2 PLC ±0.01  
3 PLC ±0.001  
4 PLC ANGLES ±0.0001  
FINISH ±

SEE NOTE 2

TE Connectivity

DTS SQUARE FLANGE ENVELOPE

SIZE A2

CAGE CODE -

DRAWING NO. ©DTS20xxx-xxP/Sx

RESTRICTED TO -

CUSTOMER DRAWING

SCALE 2.500

SHEET 1 OF 1

REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[YDTS20T25-20SB3028](#)