

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			V	REVISED PER ECO-15-002755			28FEB2015	NK	RH

SPECIFICATIONS:

MATERIALS:  
CASE: GLASS FILLED PPS, UL94V-O BROWN  
COVER: STAINLESS STEEL  
ACTUATOR BUTTON: SEE TABLE - UL94V-O  
MOVING CONTACT: COPPER ALLOY, SILVER CLAD  
MOVING CONTACT: (1571563-1,-2,-7&-8), STAINLESS STEEL,  
AG CLAD OVER NICKEL  
FIXED CONTACT/TERMINAL, COPPER ALLOY-SILVER OVER NICKEL PLATE




ELECTRICAL:  
MAX CONTACT RATING: 50MILLIAMPS@24V DC  
MIN CONTACT RATING: 10MICROAMPS@1V DC  
INITIAL CONTACT RESISTANCE: 100 MILLIOHMS MAX.  
INSULATION RESISTANCE: 100 MEGOHMS AT 100 VDC MIN.  
DIELECTRIC STRENGTH: 500 VAC 50/60 Hz FOR 1 MINUTE.  
LIFE EXPECTANCY: (SEE TABLE)



MECHANICAL:  
ACTUATION FORCE: (SEE TABLE)  
ACTUATION TRAVEL: 0.25 +0.20/-0.10 [.010 +.008/-0.004]

ENVIRONMENTAL:  
OPERATING TEMPERATURE: -35°C TO +85°C  
STORAGE TEMPERATURE: -35°C TO +85°C  
SOLDER HEAT RESISTANCE PER 109-201, CONDITION B

SOLDERABILITY:  
SPECIFICATION EIA-364-52, CLASS 1, CATEGORY 2

- 1
- TAPE AND REEL PACKAGING PER EIA 481.
- 2
- ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

( )-INDICATES MOMENTARY POSITION		
CIRCUIT CHARACTERISTICS		
CONTACT POSITION	CIRCUIT DIAGRAM	
		
OFF	(ON) 1 - 3 2 - 4	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.SARKISIAN 04MAY04		 TE Connectivity			
		CHK D.SARKISIAN 22APR94					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME  MICRO MINIATURE PUSHBUTTON SWITCH FSM JSM			
	0 PLC ± -		APVD D.SARKISIAN 22APR94				
	1 PLC ± -		PRODUCT SPEC				
	2 PLC ± 0.30[.012]		—				
	3 PLC ± -		APPLICATION SPEC				
	4 PLC ± -		—		SIZE		
	ANGLES ± 1°				CAGE CODE		
MATERIAL	FINISH		WEIGHT —		DRAWING NO		
—	—		A2		00779		
			CUSTOMER DRAWING		C=2-1437565-7		
					RESTRICTED TO		
					—		
					SCALE 8:1		
					SHEET 1 of 2		
					REV V		

THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION			2-1437565-7 , 2-1437565-7		
© COPYRIGHT 2-1437565-7 ALL RIGHTS RESERVED.								

LOC	DIST	REVISIONS								
AD	00	P	LTR	DESCRIPTION				DATE	DWN	APVD
			-	SEE SHEET 1				-	-	-

		100,000	WHITE	NYLON	260G±50G	12MM	24MM	13.00±0.10 [.512±.010]	9.40±0.10 [.370±.004]	FSM14JSMAATR	1571563-6	
		100,000	WHITE	NYLON	260G±50G	-	-	13.00±0.10 [.512±.010]	9.40±0.10 [.370±.004]	FSM14JSMAA	1571563-5	
OBSOLETE		100,000	BROWN	NYLON	100G±50G	-	-	13.00±0.10 [.512±.010]	9.40±0.10 [.370±.004]	FSM14JSML	1-1571563-0	
		100,000	WHITE	NYLON	260G±50G	12MM	24MM	9.50±0.10 [.374±.004]	5.89±0.10 [.232±.004]	FSM8JSMAATR	1-1571563-4	
OBSOLETE		100,000	WHITE	NYLON	260G±50G	-	-	9.50±0.10 [.374±.004]	5.89±0.10 [.232±.004]	FSM8JSMAA	1-1571563-3	
		100,000	BLACK	PPS	160G±50G	12MM	24MM	9.50±0.10 [.374±.004]	5.89±0.10 [.232±.004]	FSM8JSMATR	1571563-9	
		100,000	BLACK	PPS	160G±50G	-	-	9.50±0.10 [.374±.004]	5.89±0.10 [.232±.004]	FSM8JSMA	3-1437566-8	
OBSOLETE		100,000	WHITE	NYLON	260G±50G	12MM	24MM	7.01±0.10 [.276±.004]	3.40±0.10 [.134±.004]	FSM6JSMAATR	1-1571563-2	
OBSOLETE		100,000	WHITE	NYLON	260G±50G	-	-	7.01±0.10 [.276±.004]	3.40±0.10 [.134±.004]	FSM6JSMAA	1-1571563-1	
		100,000	BLACK	PPS	160G±50G	12MM	24MM	7.01±0.10 [.276±.004]	3.40±0.10 [.134±.004]	FSM6JSMATR	5-1437565-0	
		100,000	BLACK	PPS	160G±50G	-	-	7.01±0.10 [.276±.004]	3.40±0.10 [.134±.004]	FSM6JSMA	4-1437565-9	
		1,000,000	VIOLET	NYLON	70G±30G	12MM	16MM	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMXLTR	1571563-2	
		1,000,000	VIOLET	NYLON	70G±30G	-	-	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMXL	1571563-1	
		100,000	WHITE	NYLON	260G±50G	12MM	16MM	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMAATR	1571563-4	
OBSOLETE		100,000	WHITE	NYLON	260G±50G	-	-	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMAA	1571563-3	
		100,000	BLACK	PPS	160G±50G	12MM	16MM	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMATR	4-1437565-2	
		100,000	BLACK	PPS	160G±50G	-	-	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMA	4-1437565-1	
		1,000,000	BLUE	NYLON	100G±30G	12MM	16MM	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMLSTR	1571563-8	
		1,000,000	BLUE	NYLON	100G±30G	-	-	4.98±0.25 [.196±.010]	1.40±0.10 [.055±.004]	FSM4JSMLS	1571563-7	
		100,000	WHITE	NYLON	260G±50G	12MM	16MM	4.29±0.15 [.169±.006]	0.71±0.10 [.028±.004]	FSM2JSMAATR	2-1437565-9	
		100,000	WHITE	NYLON	260G±50G	-	-	4.29±0.15 [.169±.006]	0.71±0.10 [.028±.004]	FSM2JSMAA	2-1437565-8	
		100,000	GRAY	PPS	160G±50G	12MM	16MM	4.29±0.15 [.169±.006]	0.71±0.10 [.028±.004]	FSM2JSMATR	3-1437565-0	
		100,000	GRAY	PPS	160G±50G	-	-	4.29±0.15 [.169±.006]	0.71±0.10 [.028±.004]	FSM2JSMA	2-1437565-7	
		200,000	BROWN	PPS	100±50G	12MM	16MM	4.29±0.15 [.169±.006]	0.71±0.10 [.028±.004]	FSM2JSMLTR	1571527-2	
		200,000	BROWN	PPS	100±50G	-	-	4.29±0.15 [.169±.006]	0.71±0.10 [.028±.004]	FSM2JSML	1571527-1	
LIFE CYCLE	ACTUATOR COLOR	ACTUATOR MATERIAL	ACTUATION FORCE	PITCH	TAPE WIDTH	DIM 'B'			DIM 'A'		T&B PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	D.SARKISIAN	04MAY04	<div>TE Connectivity</div> <div>MICRO MINIATURE PUSHBUTTON SWITCH FSM JSM</div>						
<div>DIMENSIONS: mm [INCHES]</div> <div></div>				CHK	D.SARKISIAN	22APR94							
				TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD					D.SARKISIAN	22APR94	
				0 PLC ± - 1 PLC ± - 2 PLC ± 0.30[.012] 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC - APPLICATION SPEC -							
MATERIAL				FINISH		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
								A2	00779	C=2-1437565-7	-		
CUSTOMER DRAWING								SCALE	-	SHEET	2 of 2	REV	V

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1571527-2](#)