


REV. B
DCO-2020-09-02T11_56_41

COIL: @ 25°C	
RESISTANCE	700 OHMS $\pm 10\%$
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
	8.0 VDC MAX, 1.5 VDC MIN.
MUST RELEASE	

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE 4 MS MAX
	RELEASE 4 MS MAX
	CONTACT STABILIZATION TIME 2.5 MS MAX
	ALL OTHER REQUIREMENTS TO M39016/6-109M

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE 100,000
OPERATIONS

DR. RB 19Nov1993 CK. JMB 19Nov1993

TE TE Connectivity

CUST. QPL
CUST. NO. M39016/6-109M REV.

TE NUMBER
2-1617031-1

CII PART NUMBER
HFW 1201K45M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39016/6-109M](#)