



LOC				REVISONS			
G	14	P	ZONE	DESCRIPTION	DATE	APPD	
			A	REVISED PER 0720-0230-93	2/25/94	AMP	

METRIC
DIMENSIONS LISTED IN mm [INCHES]



AMP WIRE RANGE		UL E13288 Listed	
22-16 AWG STRANDED		22-16 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

△ STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3,260] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A PRELIMINARY DESIGN FOR REFERENCE ONLY. IT IS NOT TO BE USED FOR CONSTRUCTION OR PRODUCTION WITHOUT THE COMPLETION OF A REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN - FINISHES - TOLERANCES ON: 2 PLG DEC ± - 3 PLG DEC ± - ANGLES		DR 1-27-93 TA BIRKMAN	AMP AMP Incorporated Harrisburg, PA 17105-3508
MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 1-27-93 DA PATTERSON	
FINISH TIN PLATE 0.00254[0.000100] MIN THK PER MIL-T-10727		APPD 1-27-93 DE MILLER	
APPLICATION SPEC		APPD 1-27-93 JL MECKLEY	
NAME TERMINAL, RING TONGUE, BUDGET		SIZE CAGE CODE 00779	DRAWING NO 31087
		SCALE 10:1	

31087
PART NO

31087

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[31087](#)