



REVISONS						
		SR MJS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	G4	REVISED PER ECO-11-004587	11MAR11	RK	HMR	
	G5	REVISED PER ECO-17-008806	20FEB2018	RS	DR	



 WIRE RANGE	 Listed E13288	 LR7189 Certified
6 AWG SOLID OR STRANDED	6 AWG STRANDED	6 AWG SOLID OR STRANDED

- 1 STAMP AMP 6* APPROX AS SHOWN
- 2 NOTE DELTED.
- 3 COPPER PER ASTM B-152, ANNEALED
- 4 MEETS MS20659-109, CLASS 2
- 5 UL 486 A-B OR SAE AS7928



1000	LOOSE PIECE	170°C [338°F]	TIN PLATE 0.00254[.000100] MIN THK PER PER ASTM B545	2-321598-4
750	ON TAPE	170°C [338°F]	TIN PLATE 0.00254[.000100] MIN THK PER PER ASTM B545	 2-321598-3
100	LOOSE PIECE	170°C [338°F]	TIN PLATE 0.00254[.000100] MIN THK PER PER ASTM B545	 321598
QTY.	PACKAGE TYPE	OPERATING TEMP, MAX	FINISH	PART NO.

CUSTOMER SERVICE SYSTEMS				THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93 CHK DA PATTERSON 3-24-93 APVD JL MECKLEY 3-24-93 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —  TE Connectivity Ltd.	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		RECOMMENDED OPERATING TEMPERATURE: SEE TABLE		NAME TERMINAL, RING TONGUE, SOLISTRAND 6 AWG	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		VOLTAGE RATING: NOT APPLICABLE			
FOR ORDER ENTRY		1-800-526-5142		WIRE CROSS SECTIONAL AREA RANGE: 10.5-16.8mm ² [20,800-33,100] CIR MILS SOLID OR STRANDED		MATERIAL 	
				DIMENSIONS: MM[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .127[.005] 4 PLC ± — ANGLES ± — FINISH 	
						CUSTOMER DRAWING	
						SCALE 4:1 SHEET 1 of 1 REV G5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-321598-4](#)