

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

B

REDRAWN PER 0720-0470-95


23JAN95

LO

ME

AMP
WIRE RANGE

E13288


LR7189
Certified16-14 AWG
SOLID OR STRANDED16-14 AWG
SOLID OR STRANDED16-14 AWG
SOLID OR STRANDED

1 STAMP AMP 16-14* LOCATE APPROX AS SHOWN

2. WIRE INSUL DIA, 2.92-4.32 [.115-.170]

3. TONGUE MATL THK, 0.79±0.05 [.031±.002]

5000	ON TAPE, REEL	2-32190-1
1000	LOOSE PIECE	32190
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
170°C [338°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
mm [in]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-MATERIAL
BODY, CU, SLV, CU PER
ASTM B152FINISH
TIN PLATE
PER MIL-T-10727

DWN 23JAN95

CHK L OLMEDA

23JAN95

M ELLIS

APVD S BORTNER

23JAN95

PRODUCT SPEC

UL486A

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608NAME TERMINAL, RING,
DIAMOND GRIP,
WIRE SIZE, 16-14 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-32190

SCALE 8:1 SHEET 1 OF 1 REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-32190-1](#)