


4

3

2

1



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			H2	REVISED PER ECO-11-004820	11MAR11	RK HMR



- 1 FOR 1.27[.050] TO 2.08[.082] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK 0.46 ± 0.05 [.018 ± .002]

3 APPLIES FROM EDGE OF METAL BARREL TO CENTERLINE OF STUD HOLE.

100	LOOSE PIECE, BOX	BODY & SLEEVE: COPPER ASTM-B152 TIN PL ASTM-B545	8-323912-1
4000	323912 ON TAPE		2-323912-1
1	WIRE TERMINAL	INSULATION: NYLON ASTM-D4066 COLOR: YELLOW	323912
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 18MAR10	 TE Connectivity			
		CHK JEFF RUTH 18MAR10				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHIELUTTI 18MAR10	NAME			
	0 PLC ± -	PRODUCT SPEC	WIRE TERMINAL PIDG - RING TONGUE WIRE SIZE: 26-22			
	1 PLC ± -	APPLICATION SPEC				
MATERIAL SEE TABLE	2 PLC ± -	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	3 PLC ± 0.20 [.008]	—	A3 00779		C-323912	—
FINISH SEE TABLE	4 PLC ± -	WEIGHT	CUSTOMER DRAWING		SCALE	REV
	ANGLES ± 0° 30'	—	16:1		SHEET 1 OF 1	H2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-323912-1](#)