

330854



ZONE	LTR	DESCRIPTION	DATE	APPROVED
	P1	REVISED PER ECO-11-005294	07APR11	HMR
	P2	REV PER ECO 15-016934 CT	12-15	DE

WIRE SIZE (AWG)	CLIP	"J"	PNEUMATIC TOOL	MANUAL SERVICE TOOL
	COLOR CODE		1000 CLIPS/REEL	40 STRIPS 25 EACH
20	YELLOW	.051	2-330854-6	2-330854-4
24	RED	.029	2-330854-9	4-330854-1

CLIP SELECTION CHART


INSULATION DIA. RANGE	MANDREL NUMBER	
	PNEUMATIC TOOL (69585-1)	MANUAL SERVICE TOOL (69702)
.066-.075	69542	69561-1
.076-.085	69542-1	69561-1
.086-.095	69542-8	69561-4

MANDREL SELECTION CHART



NOTE:
1. TIN PLATE (MIL-T-10727) .0001 MIN THK
2. OBSOLETE PART NUMBER

SUGGESTED GAGE DESIGN




SCALE: 1-1

NOTE: GAGE TO VERIFY "X" DIM ONLY

DIM	GO	NO GO
"X"	.0214	.0261

AMP IDENTIFYING CODE (SEE TABLE)



UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ±.008 ANGLES ± 5°		CONTRACT NO. <i>3-23-67</i>		STE TE Connectivity	
OR <i>R. Weller</i>		CHK <i>R. Weller</i>		NAME TERMI-POINT CLIP	
MATERIAL PHOS BRONZE (QQ-P-750)		APPD <i>Swahil</i> 3-28-67		SIZE .031 X .093 SYSTEM	
HEAT TREAT		DESIGN APPD		CODE IDENT NO. 00779	
FINISH NOTE 1		OTHER APPD		NUMBER 330854	
LOC AD251P		SCALE 10:1		WT CALC ACTUAL	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-330854-6](#)