

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW


SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	F37507-000	MV-762508-2.5-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084

Quantity per roll: 2.500 PCs

Labels across: 1

Winding: outside

length of roll: 136,1 m



approx.
Ø
186
[7.323]

Ø
76,2
[3,00]

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		 TE Connectivity															
	SUBSTRATE	LABEL HEIGHT: ±0,3 [.012]		DIMENSIONS mm [INCHES]  TOLERANCES UNLESS OTHERWISE SPECIFIED <table><tr><td>0 PLC</td><td>± -</td></tr><tr><td>1 PLC</td><td>± -</td></tr><tr><td>2 PLC</td><td>± -</td></tr><tr><td>3 PLC</td><td>± -</td></tr><tr><td>4 PLC</td><td>± -</td></tr><tr><td>ANGLES</td><td>± -</td></tr></table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	CHK S. Iser / 01.04.2020 DATE					
0 PLC	± -																						
1 PLC	± -																						
2 PLC	± -																						
3 PLC	± -																						
4 PLC	± -																						
ANGLES	± -																						
	ADHESIVE	LABEL WIDTH: ±0,3 [.012]		APVD S. Iser / 01.04.2020 DATE		Name																	
	LINER	WEB WIDTH: ±0,8 [.031]		PRODUCT SPEC DATE		Tamper-proof Label Size „762508"																	
		VERTICAL REPEAT: ±0,8 [.031]*				APPLICATION SPEC DATE																	
		HORIZONTAL REPEAT: ±0,8 [.031]*				WEIGHT 0,387 g		SIZE A3		CAGE CODE C2290		DRAWING NO C-TAMPER-PROOF		RESTRICTED TO									
		PRINT POSITIONING: ±0,8 [.031]*																					
		LEFT MARGIN: ±0,4 [.016]		MATERIAL SEE TABLE		FINISH																	
		QUANTITY: -0% +2%																					
		*NON ACCUMULATING						CUSTOMER DRAWING				SHEET 1 of 1		REV A1									

All dimensions in mm [inch]

labels are centered on the liner
as long as not declared separately

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[F37507-000](#)