

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



© COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	K2	REVISED PER ECR-15-013036	03SEP2015	NK	DC



PACKAGING DETAILS:
QUANTITY PER REEL: 8000 PCS(END FEED).
SPLICES FREE






Left-sided product





Right-sided product

Rango de hilo de 0,5 a 1,5 mm²
Wire range from 0.5 to 1.5 mm²
Diametro de aislante max 3,0 mm
Max. Insulation Diameter 3.0 mm



336075-7 (REELED WITH PAPER INTERLEAVE)	Latón Brass	Preestañado Pre-Tin
336075-6	CuNiSi	Preestañado Pre-Tin
336075-5	Acero Steel	Preniquelado Pre-Ni
336075-3	Latón Brass	Preestañado Pre-Tin
336075-1	Latón Brass	-
Guion Dash	Material	Acabado Finish



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. Saló 22 Dec 04	 TE Connectivity		
		CHK L. L 22 Dec 04			
		APVD -			
		PRODUCT SPEC 108-22128 Brass 108-22150 Pre-Ni Steel			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME E-SPRING CONTACT 6,35 Receptaculo 6.35 Receptacle E-SPRING CONTACT		
	0 PLC ±0.5	1 PLC ±0.5	SIZE A3		
	2 PLC ±-	3 PLC ±-	CAGE CODE 00779		
MATERIAL Table		FINISH Table	DRAWING NO C-336075		
			RESTRICTED TO -		
			SCALE 4:1		
			SHEET 1 OF 1		
			REV K2		
			Customer Drawing		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[336075-5](#)