











MOUNTING CONDITIONS



SCALE 2:1



DETAIL Y
SCALE 5:1

DETAIL Z
SCALE 5:1

Notice :

- 1) Permitted Torque 6 Nm WHEN MIN. 4 TURNS
- 2) Socket Housing
TE Interface 2 Pos. MQS Code A ,
appropriate for Socket Housing 2 Pos. MQS,
TE PART NO. 1-967644-1
PRESCRIBED WIRE CROSS SECTION = 0,35mm² MIN
- 3) HEXAGON SOCKET BOTTOM HEAD SCREW EN ISO 7380 M6 WITH
WASHER ISO 7090/ 7089

PART ALIAS	TCPN	REV
V23720-A0101-B001	2-1904136-5	F

PROPRIETARY THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.				CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD		PAPER SIZE A1
APPLICABLE SPEC. :				FINISH		
				DIMENSIONS APPLY PLATING		
				SCALE 1:1 WEIGHT 600g		
				MATERIAL		

				PART NAME		
				EVC 250 - 800 , HV-RELAY WITH CONNECTOR		
				DWG NO.		
				V23720-A0101-B001-CD		
				SHT.		
				1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1904136-5](#)