






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AC	REVISED PER ECO-19-006997	15MAY2019	BKW	SF
	AC1	REVISED PER ECO-19-006997	24JUL2019	BKW	SF




- 1 0.00076 [.000030] MIN THK GOLD IN LOCALIZED PLATE AREA AND 0.000127 [.000005] MIN THK GOLD FLASH ON REMAINDER OF CONTACT OVER 0.00127 [.000050] MIN THK NICKEL UNDERPLATE.
- 2 0.00076 [.000030] MIN THK GOLD IN LOCALIZED PLATE AREA OVER 0.00127 [.000050] MIN THK NICKEL UNDERPLATE.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. WIRE RANGE: 20-14 AWG
INSULATION RANGE: 3.30-5.08 [.130-.200] DIAMETER

Ø 2.071-2.133
[.0815-.0840]



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

350552-7	GOLD	2	0.30 [.012] BRASS	350538-7
350552-6	GOLD	2	0.30 [.012] PH BZ	350538-6
350552-3	TIN		0.30 [.012] PH BZ	350538-3
350552-2	GOLD	1	0.30 [.012] BRASS	350538-2
350552-1	TIN		0.30 [.012] BRASS	350538-1
LOOSE PIECE (REF)	FINISH		MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. WEAVER 15MAY2019	TE Connectivity		
DIMENSIONS: mm [IN]		CHK S. FERNANDES 15MAY2019			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.20 [.008] 4 PLC ± ANGLES ± FINISH	APVD T. BENCHOFF 15MAY2019	NAME PIN, MATE-N-LOK, UNIVERSAL		
		PRODUCT SPEC 108-1031	SIZE A2		
		APPLICATION SPEC 114-1010			
MATERIAL SEE TABLE	SEE TABLE	WEIGHT -	CAGE CODE 00779	DRAWING NO 350538	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV AC1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[350538-2](#)