



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	ADDED 2-35135-2 PER PR 94-6	2/2/94	DKS	DAP
	H1	REVISED PER ECO-17-018181	12DEC2017	RS	DR



AMP WIRE RANGE	E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	MS 20659-166 CLASS 2

STAMP AMP 12-10* APPROX AS SHOWN.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm ² [5,180-13,100] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 3-17-93				
		APVD DE MILLER 3-17-93				
		PRODUCT SPEC UL486 A-B OR SAE AS7928				
MATERIAL COPPER PER ASTM B-152 ANNEALED		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± - FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545	NAME DE MILLER	SIZE A2	CAGE CODE 00779	DRAWING NO C=35135
		WEIGHT -	APPLICATION SPEC -	RESTRICTED TO -	SHEET 1 OF 1	
CUSTOMER DRAWING				SCALE 4:1	REV H1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-35135-2](#)