



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		M10	REVISED PER ECR-19-006969	22AUG2019	BDA	DS



- 1 ALL DIMENSIONS APPLY TO A MOISTURIZED HOUSING.
- 2 PRELIMINARY – NOT FOR PRODUCTION
- 3 OFFERED FOR CONSIDERATION IN "NON-DRIP" HOUSING MATERIAL APPLICATIONS.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING I PER D.RENAUD/D.SINIS
- 5 PREPRODUCTION-FASR REQUIRED

SUGGESTED MATING TAB










- 1 – MATL: ½ H BRASS OR NICKEL PL STEEL.
- 2 – NO BURRS PERMISSIBLE AT HOLE.
- 3 – MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 – TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225° F
- 5 – HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/3/96		 TE Connectivity								
DIMENSIONS: mm [INCHES]		CHK MS FEHER 7/3/96										
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J GILLISPIE 7/3/96		NAME HOUSING, RECEPTACLE, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES —							
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —									
	MATERIAL SEE TABLE		APPLICATION SPEC —						SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	FINISH SEE TABLE		WEIGHT						A2	00779	C=521120	—
CUSTOMER DRAWING				SCALE		SHEET		REV				
				5:1		1 of 2		M10				



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- -
© COPYRIGHT - By -		ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

NATURAL	66 NYLON, V0 NATURAL, GWT		3-521120-1
BROWN	66/6 NYLON, V0		2-521120-5
YELLOW	66/6 NYLON, V0		2-521120-4
GREEN	66/6 NYLON, V0		2-521120-3
RED	66/6 NYLON, V0		2-521120-2
BLUE	66/6 NYLON, V0		2-521120-1
BROWN	6/6 NYLON, V2		2-521120-0
YELLOW	6/6 NYLON, V2		1-521120-9
GREEN	6/6 NYLON, V2		1-521120-8
NATURAL	6/6 NYLON, V2		1-521120-7
BLACK	66/6 NYLON, V0		1-521120-6
NATURAL	 66/6 OR 66 NYLON, V0		1-521120-5
NATURAL	6/6 NYLON, V0		1-521120-4
NATURAL	66/6 OR 66 NYLON, V0		1-521120-3
YELLOW	6/6 NYLON		1-521120-2
BLUE	6/6 NYLON		1-521120-1
GREEN	6/6 NYLON		1-521120-0
RED	6/6 NYLON		-521120-9
BLACK	6/6 NYLON		521120-8
NATURAL	6/6 NYLON		521120-7
BLACK	4/6 NYLON		521120-6
RED	6/6 NYLON		521120-5
BLUE	6/6 NYLON		521120-4
PUTTY	6/6 NYLON		-521120-2-
NATURAL	6/6 NYLON		521120-1
COLOR	MATERIAL		PART NO

4
OBSOLETE

4 OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/3/96		 TE Connectivity									
		CHK MS FEHER 7/3/96											
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HOUSING, RECEPTACLE, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES —		SIZE A2		CAGE CODE 00779		DRAWING NO C-521120		RESTRICTED TO —	
		APVD J GILLISPIE 7/3/96											
		PRODUCT SPEC —											
		APPLICATION SPEC —											
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —									
CUSTOMER DRAWING				SCALE 5:1		SHEET 2 of 2		REV M10					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-521120-1](#)