



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT — TE Connectivity Ltd.	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REV & REDRAWN PER ECR 10-005247	09MAR10	JR	TM
	G1	REVISED PER ECO-17-008114	31MAY2018	RS	DR



- 1 FOR 1.270 TO 2.083[.050 TO .082]  
WIRE INSULATION DIA
- 2 BODY MATERIAL THK: 0.457±0.051[.018±.002]
- 3 APPLIES FROM THE METAL EDGE OF THE  
BARREL TO THE CENTER OF THE STUD
- 4 MATERIAL:  
BODY: PHOS BRONZE PER ASTM-B103  
SLEEVE: COPPER PER ASTM-B152  
INSULATION: NYLON PER ASTM-D4066 TYPE 1
- 5 FINISH:  
BODY & SLEEVE: TIN PLATE PER ASTM-B545  
INSULATION: COLOR - YELLOW
- 6 STAMP AMP 2S APPROX AS SHOWN

1000	WIRE TERMINAL	52921
QTY	DESCRIPTION	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 09MAR10	TE Connectivity Ltd.			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ± 5° ANGLES FINISH	CHK TOM MICHIELUTTI 09MAR10				
					APVD TOM MICHIELUTTI 09MAR10	NAME			
FOR APPLICATION	TOOLING ASSISTANCE CENTER	300 V MAX			PRODUCT SPEC	WIRE TERMINAL, PIDG, SPRING SPADE WIRE SIZE: 26-22			
TOOLING INFORMATION	1-800-722-1111				APPLICATION SPEC 114-2157				
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE, 0.10-0.41mm²[202-810] CIR MILS STRANDED	MATERIAL 4	FINISH 5	WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-52921	RESTRICTED TO -
CUSTOMER DRAWING							SCALE 8:1	SHEET 1 of 1	REV G1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[52921](#)