





RECOMENDED HOLE LAYOUT
FOR BOTTOM ENTRY OR PASS
THROUGH APPLICATIONS

- 1 TE CONNECTIVITY LOGO AND CSA LOGO ARE MOLDED INTO THE HOUSING.
- 2 TOLERANCE NON-CUMULATIVE.
- 3 DUPLEX PLATED: 0.00076 (.000030) GOLD IN CONTACT AREA, .00381-.00762 (.000150-.000300) BRIGHT TIN-LEAD ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- 4 THESE DIMENSIONS PERTAIN TO CAVITY C/L'S ONLY, NOT TO CONTACT LOCATIONS.
- 5 NO PART NUMBER MARKING REQUIRED ON THIS PART NUMBER.
- 6 HOUSING: FLAME RETARDANT GLASS FILLED POLYESTER - BLACK.
CONTACTS: PHOS. BRONZE.
- 7 POINT OF CONTACT DIMENSION.
- 8 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE CONTACT BEAMS).
- 9 DUPLEX PLATED: 0.00076 (.000030) GOLD DUPLEX IN CONTACT AREA,
0.00381-0.00762 (.000150-.000300) MATTE TIN ON LEADS, ALL OVER
0.00127 (.000050) MIN NICKEL.
- 10 ROHS 2002/95/EC COMPLIANT
- 11 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN.
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

5	OBSOLETE	9	1.300	1.200	26	10	9-534236-1	
	OBSOLETE	9	4.000	3.900	80	10	9-534236-0	
		9	3.900	3.800	78	10	8-534236-9	
		9	3.800	3.700	76	10	8-534236-8	
		9	3.700	3.600	74	10	8-534236-7	
		9	3.600	3.500	72	10	8-534236-6	
		9	3.500	3.400	70	10	8-534236-5	
		9	3.400	3.300	68	10	8-534236-4	
		9	3.300	3.200	66	10	8-534236-3	
		9	3.200	3.100	64	10	8-534236-2	
		9	3.100	3.000	62	10	8-534236-1	
		9	3.000	2.900	60	10	8-534236-0	
		9	2.900	2.800	58	10	7-534236-9	
		9	2.800	2.700	56	10	7-534236-8	
		9	2.700	2.600	54	10	7-534236-7	
		9	2.600	2.500	52	10	7-534236-6	
		9	2.500	2.400	50	10	7-534236-5	
		9	2.400	2.300	48	10	7-534236-4	
		9	2.300	2.200	46	10	7-534236-3	
	9	2.200	2.100	44	10	7-534236-2		
9	2.100	2.000	42	10	7-534236-1			
5		9	2.000	1.900	40	10	7-534236-0	
		9	1.900	1.800	38	10	6-534236-9	
	OBSOLETE	9	1.800	1.700	36	10	6-534236-8	
		9	1.700	1.600	34	10	6-534236-7	
	OBSOLETE	9	1.600	1.500	32	10	6-534236-6	
		9	1.500	1.400	30	10	6-534236-5	
	OBSOLETE	9	1.400	1.300	28	10	6-534236-4	
		9	1.300	1.200	26	10	6-534236-3	
		9	1.200	1.100	24	10	6-534236-2	
	OBSOLETE	9	1.100	1.000	22	10	6-534236-1	
		9	1.000	.900	20	10	6-534236-0	
	OBSOLETE	9	.900	.800	18	10	5-534236-9	
		9	.800	.700	16	10	5-534236-8	
		9	.700	.600	14	10	5-534236-7	
		9	.600	.500	12	10	5-534236-6	
	5	9	.500	.400	10	10	5-534236-5	
	5	OBSOLETE	9	.400	.300	8	10	5-534236-4
	5	OBSOLETE	9	.300	.200	6	10	5-534236-3
	5	OBSOLETE	9	.200	.100	4	10	5-534236-2
	5	OBSOLETE	9	.100	-	2	10	5-534236-1
	FINISH		A	B	NO OF POSN	PART NO.		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. BOLES 19-11-92	TE Connectivity ASSEMBLY, MOD II DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED, CLOSED ENTRY, SHORT PT. CONTACTS					
DIMENSIONS: mm [INCHES]		CHK T. KINSEY 19-11-92						
		APVD -						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC 108-25026 APPLICATION SPEC 114-25018 WEIGHT -						
MATERIAL 6		FINISH 39		SIZE A2	CAGE CODE 00779	DRAWING NO C=534236	RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 4:1	SHEET 2 OF 2	REV V2

5	12	OBSOLETE	3	1.300	1.200	26	4-534236-1
	OBSOLETE	3	4.000	3.900	80	4-534236-0	
		3	3.900	3.800	78	3-534236-9	
		3	3.800	3.700	76	3-534236-8	
		3	3.700	3.600	74	3-534236-7	
		3	3.600	3.500	72	3-534236-6	
		3	3.500	3.400	70	3-534236-5	
		3	3.400	3.300	68	3-534236-4	
		3	3.300	3.200	66	3-534236-3	
		3	3.200	3.100	64	3-534236-2	
	12	OBSOLETE	3	3.100	3.000	62	3-534236-1
		3	3.000	2.900	60	3-534236-0	
	OBSOLETE	3	2.900	2.800	58	2-534236-9	
		3	2.800	2.700	56	2-534236-8	
		3	2.700	2.600	54	2-534236-7	
	12	OBSOLETE	3	2.600	2.500	52	2-534236-6
		3	2.500	2.400	50	2-534236-5	
		3	2.400	2.300	48	2-534236-4	
	12	OBSOLETE	3	2.300	2.200	46	2-534236-3
		3	2.200	2.100	44	2-534236-2	
12	OBSOLETE	3	2.100	2.000	42	2-534236-1	
	3	2.000	1.900	40	2-534236-0		
	3	1.900	1.800	38	1-534236-9		
12	OBSOLETE	3	1.800	1.700	36	1-534236-8	
	3	1.700	1.600	34	1-534236-7		
	3	1.600	1.500	32	1-534236-6		
	3	1.500	1.400	30	1-534236-5		
	3	1.400	1.300	28	1-534236-4		
	3	1.300	1.200	26	1-534236-3		
	3	1.200	1.100	24	1-534236-2		
12	OBSOLETE	3	1.100	1.000	22	1-534236-1	
	3	1.000	.900	20	1-534236-0		
	3	.900	.800	18	534236-9		
	3	.800	.700	16	534236-8		
	3	.700	.600	14	534236-7		
	3	.600	.500	12	534236-6		
	3	.500	.400	10	5 534236-5		
	3	.400	.300	8	5 534236-4		
OBSOLETE	3	.300	.200	6	5 534236-3		
	3	.200	.100	4	5 534236-2		
	3	.100	-	2	5 534236-1		
	FINISH		A	B	NO OF POSN	PART NO.	

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-534236-6](#)