



MODEL 44115

Thermistor with Teflon® Sheath

- 2" (51mm) Teflon® Sheath for Hostile Environments
- 1 Meg-ohm Resistance @ 25°C
- Interchangeable $\pm 0.2^{\circ}\text{C}$, 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- Thermally conductive epoxy coating
- 32 AWG, 3" (7.6 cm) long Silver plated copper leads
- One inner lead is sleeved with Teflon® tubing for insulation
- A nickel stiffening wire allows shaping of the sheath
- RoHS Compliant

FEATURES

- Teflon® Sheath
- 1 Meg-ohm Resistance @ 25°C
- Interchangeability
- Good Long Term Stability
- High Sensitivity
- Thermally Conductive Epoxy Coating
- RoHS Compliance

APPLICATIONS

- Harsh Chemical Environments
- High-range Temperature Applications
- Tight Tolerance Applications
- General Applications Requiring Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments
- Allows use in Applications World-wide


MODEL 44115

Thermistor with Teflon® Sheath

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C	Ohms	1,000,000
Tolerance 0°C to 70°C	°C	± 0.2
Beta Value 25/85	K	4803
Tolerance on Beta Value	%	0.8
Time response in air	Seconds	< 25
Insulation Resistance (Min. of 100 Mohms for 1 sec.)	Volts	500

MECHANICAL DETAILS



TYPICAL PERFORMANCE CURVES (RESISTANCE OF INDIVIDUAL THERMISTORS)

Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms
0	1088.0	30	236.4	60	63.70	90	20.45	120	7.594
1	1030.0	31	225.6	61	61.17	91	19.75	121	7.364
2	975.3	32	215.3	62	58.75	92	19.07	122	7.142
3	923.8	33	205.5	63	56.44	93	18.41	123	6.927
4	875.2	34	196.2	64	54.23	94	17.78	124	6.720
5	829.5	35	187.4	65	52.12	95	17.18	125	6.519
6	786.3	36	179.0	66	50.10	96	16.60	126	6.326
7	745.6	37	171.0	67	48.17	97	16.04	127	6.139
8	707.2	38	163.5	68	46.32	98	15.50	128	5.958
9	671.0	39	156.3	69	44.54	99	14.98	129	5.784
10	636.8	40	149.4	70	42.85	100	14.48	130	5.615
11	604.5	41	142.9	71	41.23	101	14.00	131	5.452
12	574.0	42	136.7	72	39.67	102	13.54	132	5.294
13	545.2	43	130.8	73	38.18	103	13.09	133	5.141
14	518.0	44	125.1	74	36.75	104	12.66	134	4.994
15	492.3	45	119.8	75	35.39	105	12.25	135	4.851
16	468.0	46	114.7	76	34.08	106	11.86	136	4.713
17	444.9	47	109.8	77	32.82	107	11.47	137	4.580
18	423.2	48	105.2	78	31.62	108	11.11	138	4.450
19	402.6	49	100.8	79	30.46	109	10.75	139	4.325
20	383.1	50	96.54	80	29.35	110	10.41	140	4.204
21	364.6	51	92.52	81	28.29	111	10.08	141	4.087
22	347.1	52	88.69	82	27.27	112	9.763	142	3.974
23	330.6	53	85.04	83	26.29	113	9.456	143	3.864
24	314.9	54	81.55	84	25.35	114	9.161	144	3.757
25	300.0	55	78.22	85	24.45	115	8.876	145	3.654
26	285.9	56	75.04	86	23.59	116	8.601	146	3.555
27	272.5	57	72.01	87	22.76	117	8.336	147	3.458
28	259.8	58	69.11	88	21.96	118	8.080	148	3.364
29	247.8	59	66.34	89	21.19	119	7.832	149	3.274
								150	3.186

MODEL 44115

Thermistor with Teflon® Sheath

ORDERING INFORMATION

Part Number	Description	Ω @25°C
095410	44115 THERM,TEF ENCAPSULATED	1,000,000

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.tlse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[11029043-00](#)