




- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE
- 2 CONTACT: DUPLEX PLATED 0.76μm[.000030] GOLD IN CONTACT AREA,
3.81–7.62μm[.000150–.000300] BRIGHT TIN–LEAD ON LEADS,ALL OVER
1.27μm[.000050] MINIMUM NICKEL.
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY – NOT TO
CONTACT LOCATIONS
- 4 MARK PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE
LOCATION SHOWN, EITHER SIDE.
- 5 TOLERANCE IS NON–CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE LOGO.
- 7 POINT–OF–MEASUREMENT DIMENSION FOR PLATING THICKNESS
(INSIDE CONTACT BEAM).
- 8 POINT–OF–CONTACT DIMENSION.
- 9 TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING,
THIS LOCATION.
- 10 NO PART NUMBER MARKING REQUIRED FOR THIS PART.
- 11 CONTACT: DUPLEX PLATED 0.76 MICROMETERS (.000030) GOLD IN CONTACT
AREA, 3.81–7.62 MICROMETERS (.000150–.000300) MATTE TIN ON LEADS,
ALL OVER 1.27 MICROMETERS (.000050) MINIMUM NICKEL
- 12 ROHS 2002/95/EC COMPLIANT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK J.OLSON 06NOV02			
		APVD J.OLSON 06NOV02	NAME		
		PRODUCT SPEC 108-25022	RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU		
MATERIAL		APPLICATION SPEC 114-25018	SIZE A2	CAGE CODE 00779	DRAWING NO C=535542
		FINISH	WEIGHT -	RESTRICTED TO -	
1		2 11	CUSTOMER DRAWING		
			SCALE 4:1	SHEET 1 OF 2	REV U5

D

C

B

A

D

C

B

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	APVD
		-	-	SEE SHEET 1	-	-

	99.06	[3.900]	101.60	[4.000]	80		9-535542-0	
	96.52	[3.800]	99.06	[3.900]	78		8-535542-9	
	93.98	[3.700]	96.52	[3.800]	76		8-535542-8	
	91.44	[3.600]	93.98	[3.700]	74		8-535542-7	
	88.90	[3.500]	91.44	[3.600]	72		8-535542-6	
	86.36	[3.400]	88.90	[3.500]	70		8-535542-5	
	83.82	[3.300]	86.36	[3.400]	68		8-535542-4	
	81.28	[3.200]	83.82	[3.300]	66		8-535542-3	
	78.74	[3.100]	81.28	[3.200]	64		8-535542-2	
	76.20	[3.000]	78.74	[3.100]	62		8-535542-1	
	73.66	[2.900]	76.20	[3.000]	60		8-535542-0	
	71.12	[2.800]	73.66	[2.900]	58		7-535542-9	
	68.58	[2.700]	71.12	[2.800]	56		7-535542-8	
	66.04	[2.600]	68.58	[2.700]	54		7-535542-7	
	63.50	[2.500]	66.04	[2.600]	52		7-535542-6	
	60.96	[2.400]	63.50	[2.500]	50		7-535542-5	
	58.42	[2.300]	60.96	[2.400]	48		7-535542-4	
	55.88	[2.200]	58.42	[2.300]	46		7-535542-3	
	53.34	[2.100]	55.88	[2.200]	44		7-535542-2	
	50.80	[2.000]	53.34	[2.100]	42		7-535542-1	
	48.26	[1.900]	50.80	[2.000]	40		7-535542-0	
	45.72	[1.800]	48.26	[1.900]	38		6-535542-9	
	43.18	[1.700]	45.72	[1.800]	36		6-535542-8	
	40.64	[1.600]	43.18	[1.700]	34		6-535542-7	
	38.10	[1.500]	40.64	[1.600]	32		6-535542-6	
	35.56	[1.400]	38.10	[1.500]	30		6-535542-5	
	33.02	[1.300]	35.56	[1.400]	28		6-535542-4	
	30.48	[1.200]	33.02	[1.300]	26		6-535542-3	
	27.94	[1.100]	30.48	[1.200]	24		6-535542-2	
	25.40	[1.000]	27.94	[1.100]	22		6-535542-1	
	22.86	[.900]	25.40	[1.000]	20		6-535542-0	
	20.32	[.800]	22.86	[.900]	18		5-535542-9	
	17.78	[.700]	20.32	[.800]	16		5-535542-8	
	15.24	[.600]	17.78	[.700]	14		5-535542-7	
	12.70	[.500]	15.24	[.600]	12		5-535542-6	
		10.16	[.400]	12.70	[.500]	10		5-535542-5
		7.62	[.300]	10.16	[.400]	8		5-535542-4
		5.08	[.200]	7.62	[.300]	6		5-535542-3
		2.54	[.100]	5.08	[.200]	4		5-535542-2
		-	2.54	[.100]	2			5-535542-1
FINISH	B	A	NO OF POSN	PART NUMBER				

		99.06	[3.900]	101.60	[4.000]	80	4-535542-0
		96.52	[3.800]	99.06	[3.900]	78	3-535542-9
		93.98	[3.700]	96.52	[3.800]	76	3-535542-8
		91.44	[3.600]	93.98	[3.700]	74	3-535542-7
		88.90	[3.500]	91.44	[3.600]	72	3-535542-6
		86.36	[3.400]	88.90	[3.500]	70	3-535542-5
		83.82	[3.300]	86.36	[3.400]	68	3-535542-4
		81.28	[3.200]	83.82	[3.300]	66	3-535542-3
		78.74	[3.100]	81.28	[3.200]	64	3-535542-2
		76.20	[3.000]	78.74	[3.100]	62	3-535542-1
		73.66	[2.900]	76.20	[3.000]	60	3-535542-0
		71.12	[2.800]	73.66	[2.900]	58	2-535542-9
		68.58	[2.700]	71.12	[2.800]	56	2-535542-8
		66.04	[2.600]	68.58	[2.700]	54	2-535542-7
		63.50	[2.500]	66.04	[2.600]	52	2-535542-6
		60.96	[2.400]	63.50	[2.500]	50	2-535542-5
		58.42	[2.300]	60.96	[2.400]	48	2-535542-4
		55.88	[2.200]	58.42	[2.300]	46	2-535542-3
		53.34	[2.100]	55.88	[2.200]	44	2-535542-2
		50.80	[2.000]	53.34	[2.100]	42	2-535542-1
		48.26	[1.900]	50.80	[2.000]	40	2-535542-0
		45.72	[1.800]	48.26	[1.900]	38	1-535542-9
		43.18	[1.700]	45.72	[1.800]	36	1-535542-8
		40.64	[1.600]	43.18	[1.700]	34	1-535542-7
		38.10	[1.500]	40.64	[1.600]	32	1-535542-6
		35.56	[1.400]	38.10	[1.500]	30	1-535542-5
		33.02	[1.300]	35.56	[1.400]	28	1-535542-4
		30.48	[1.200]	33.02	[1.300]	26	1-535542-3
		27.94	[1.100]	30.48	[1.200]	24	1-535542-2
		25.40	[1.000]	27.94	[1.100]	22	1-535542-1
		22.86	[.900]	25.40	[1.000]	20	1-535542-0
		20.32	[.800]	22.86	[.900]	18	535542-9
		17.78	[.700]	20.32	[.800]	16	535542-8
		15.24	[.600]	17.78	[.700]	14	535542-7
		12.70	[.500]	15.24	[.600]	12	535542-6
		10.16	[.400]	12.70	[.500]	10	535542-5
		7.62	[.300]	10.16	[.400]	8	535542-4
		5.08	[.200]	7.62	[.300]	6	535542-3
		2.54	[.100]	5.08	[.200]	4	535542-2
		-		2.54	[.100]	2	535542-1
FINISH	B	A	NO OF POSN	PART NUMBER			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	06NOV2002	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK J.OLSON	06NOV02				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD J.OLSON	06NOV02	NAME			
		PRODUCT SPEC		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU			
		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL 	FINISH 	108-25022		A2	00779	C=535542	-
CUSTOMER DRAWING			WEIGHT -	SCALE 1:1	SHEET 2 of 2	REV U5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-535542-2](#)