



D

C

B

A



- FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7532.
- SWITCH SHOWN IN OPEN POSITION.
- ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLUE.
- LASER MARKING WILL VARY ON 2 AND 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.
- .315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300+.010 -.000 AT MOUNTING SURFACE.
- STRIPPABLE TRANSPARENT SEAL, SEE FIG 1.
- STRIPPABLE TRANSPARENT SEAL, SEE FIG 1.
- MATERIAL: HOUSING & ROCKERS- POLYESTER CONTACTS & SOLDER LEAD-COPPER ALLOY
- FINISH: CONTACTS- GOLD OVER NICKEL SOLDER LEAD- TIN OVER NICKEL
- ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002 /95/EC OF 27JAN2003(ROHS).
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- MARKS WILL BE ADDED BY LASER MARK PROCESS.




FIG 1




FIG 2




FIG 3




FIG 4




FIG 5




FIG 6






FIG 7

<div><div>11</div><div>OBSOLETE</div></div>	FIG 6	1.08	10	6-5435640-1	
		.58	5	6-5435640-0	
		FIG 7	.48	4	5-5435640-9
			.88	8	5-5435640-8
<div><div>11</div><div>OBSOLETE</div></div>	FIG 5	.98	9	5-5435640-7	
		.68	6	5-5435640-6	
		.58	5	5-5435640-5	
		.48	4	5-5435640-4	
<div>OBSOLETE</div>	FIG 2	.88	8	5-5435640-3	
	FIG 5	1.08	10	5-5435640-1	
	FIG 3	.88	8	5-5435640-0	
		.88	8	4-5435640-9	
.58		5	4-5435640-8		
<div><div>11</div><div>OBSOLETE</div></div>	NONE	1.08	10	4-5435640-7	
	AS SHOWN	1.28	12	4-5435640-3	
		1.08	10	4-5435640-1	
		.98	9	4-5435640-0	
.88		8	3-5435640-9		
.78		7	3-5435640-8		
.68		6	3-5435640-7		
.58		5	3-5435640-6		
.48		4	3-5435640-5		
1.28		12	3-5435640-2		
FIG 4	.38	3	3-5435640-0		
	.28	2	2-5435640-9		
AS SHOWN	1.08	10	5435640-7		
	.98	9	5435640-6		
	.88	8	5435640-5		
	.68	6	5435640-4		
	.58	5	5435640-3		
	.48	4	5435640-2		
	.78	7	5435640-1		
TOP MARKING	A	NO OF POSN	PART NO.		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV 08JAN2005	 TE Connectivity					
		CHK M. SARVER 13SEP05						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. SARVER 13SEP05	NAME	SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, STANDARD				
		PRODUCT SPEC						
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - ± -	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT					A1	00779
MATERIAL SEE NOTES		CUSTOMER DRAWING	SCALE	4:1	SHEET	1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5435640-1](#)