


12	30.48[1.200]	33.02[1.300]	13	7-5535676-2
	162.56[6.400]	165.10[6.500]	65	6-5535676-4
	160.02[6.300]	162.56[6.400]	64	6-5535676-3
	157.48[6.200]	160.02[6.300]	63	6-5535676-2
	154.94[6.100]	157.48[6.200]	62	6-5535676-1
	152.40[6.000]	154.94[6.100]	61	6-5535676-0
	149.86[5.900]	152.40[6.000]	60	5-5535676-9
	147.32[5.800]	149.86[5.900]	59	5-5535676-8
	144.78[5.700]	147.32[5.800]	58	5-5535676-7
	139.70[5.500]	144.78[5.700]	57	5-5535676-6
	139.70[5.500]	142.24[5.600]	56	5-5535676-5
	137.16[5.400]	139.70[5.500]	55	5-5535676-4
	134.62[5.300]	137.16[5.400]	54	5-5535676-3
	132.08[5.200]	134.62[5.300]	53	5-5535676-2
	129.54[5.100]	132.08[5.200]	52	5-5535676-1
	127.00[5.000]	129.54[5.100]	51	5-5535676-0
	124.46[4.900]	127.00[5.000]	50	4-5535676-9
	121.92[4.800]	124.46[4.900]	49	4-5535676-8
	119.38[4.700]	121.92[4.800]	48	4-5535676-7
	116.84[4.600]	119.38[4.700]	47	4-5535676-6
	114.30[4.500]	116.84[4.600]	46	4-5535676-5
	111.76[4.400]	114.30[4.500]	45	4-5535676-4
	109.22[4.300]	111.76[4.400]	44	4-5535676-3
	106.68[4.200]	109.22[4.300]	43	4-5535676-2
	104.14[4.100]	106.68[4.200]	42	4-5535676-1
	101.16[4.000]	104.14[4.100]	41	4-5535676-0
	99.06[3.900]	101.16[4.000]	40	3-5535676-9
	96.52[3.800]	99.06[3.900]	39	3-5535676-8
	93.98[3.700]	96.52[3.800]	38	3-5535676-7
	91.44[3.600]	93.98[3.700]	37	3-5535676-6
	88.90[3.500]	91.44[3.600]	36	3-5535676-5
	86.36[3.400]	88.90[3.500]	35	3-5535676-4
	83.82[3.300]	86.36[3.400]	34	3-5535676-3
	81.28[3.200]	83.82[3.300]	33	3-5535676-2
	78.74[3.100]	81.28[3.200]	32	3-5535676-1
	76.20[3.000]	78.74[3.100]	31	3-5535676-0
	73.66[2.900]	76.20[3.000]	30	2-5535676-9
	71.12[2.800]	73.66[2.900]	29	2-5535676-8
	68.58[2.700]	71.12[2.800]	28	2-5535676-7
	66.04[2.600]	68.58[2.700]	27	2-5535676-6
	63.50[2.500]	66.04[2.600]	26	2-5535676-5
	60.96[2.400]	63.50[2.500]	25	2-5535676-4
	58.42[2.300]	60.96[2.400]	24	2-5535676-3
	55.88[2.200]	58.42[2.300]	23	2-5535676-2
	53.34[2.100]	55.88[2.200]	22	2-5535676-1
	50.80[2.000]	53.34[2.100]	21	2-5535676-0
	48.26[1.900]	50.80[2.000]	20	1-5535676-9
	45.72[1.800]	48.26[1.900]	19	1-5535676-8
	43.18[1.700]	45.72[1.800]	18	1-5535676-7
	40.64[1.600]	43.18[1.700]	17	1-5535676-6
	38.10[1.500]	40.64[1.600]	16	1-5535676-5
	35.56[1.400]	38.10[1.500]	15	1-5535676-4
	33.02[1.300]	35.56[1.400]	14	1-5535676-3
	30.48[1.200]	33.02[1.300]	13	1-5535676-2
	27.94[1.100]	30.48[1.200]	12	1-5535676-1
	25.40[1.000]	27.94[1.100]	11	1-5535676-0
	22.86[.900]	25.40[1.000]	10	5535676-9
	17.78[.700]	22.86[.900]	9	5535676-8
	17.78[.700]	20.32[.800]	8	5535676-7
	15.24[.600]	17.78[.700]	7	5535676-6
	12.70[.500]	15.24[.600]	6	5535676-5
8	10.16[.400]	12.70[.500]	5	5535676-4
8	7.62[.300]	10.16[.400]	4	5535676-3
9	5.08[.200]	7.62[.300]	3	5535676-2
9	2.54[.100]	5.08[.200]	2	85535676



COLLIDED DOCUMENT.		BWN BSV CHK —		OSN0V04 —		NO. OF POSN		ASSEMBLY PART NUMBER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		OLSON APVD J. OLSON PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		NAME AMPMODU MODII RECP. ASSY., HORIZ., .100CL, 1 ROW CLOSED ENTRY, SPOC, END STACK —		 TE Connectivity			
C ± — C ± — C ± 0.1% [.005] ES ± —		SIZE A1		GAGE CODE 100779		DRAWING NO C-5535676		RESTRICTED TO —	
SH 		CUSTOMER DRAWING		SCALE 5:1		SHEET 1 of 1		REV A0	

-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG BSV		05N0V04		 TE Connectivity	
DIMENSIONS: UNLESS OTHERWISE SPECIFIED:		CHG OLSON		REV 0			
mm		APD OLSON		NAME		AMPMODU MODII RECP. ASSY., HORIZ., .100CL, 1 ROW CLOSED ENTRY, SPOC, END STACK —	
		PRODUCT SPEC					
0 PLG ± — 1 PLG ± — 2 PLG ± — 3 PLG ± 0.13[.005] ANGLES ± —		APPLICATION SPEC		SIZE		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO		RESTRICTED TO	
		—		A1 00779		C=5535676	
		CUSTOMER DRAWING		SCALE		SHEET	
				5:1		1 OF 1	
						REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5535676-4](#)