



01-22

AMP

UL

EC

$\varnothing 6.858$   
[ $\varnothing .270$ ]  
MAX  
IN CRIMP AREA

INSULATION

BODY

1

$\varnothing 11.582$   
[ $\varnothing .456$ ]  
MAX

24.892  
[.980]  
MAX

AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER  
1-800-522-6752

FOR APPLICATION  
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER  
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING  
TEMPERATURE:  
  
150° C [302°F] MAX

VOLTAGE RATING:  
600V MAX (BUILDING & WIRING)  
1000V MAX (FIXTURES & SIGNS)

CIRCULAR MIL AREA:  
  
1.65-6.64mm<sup>2</sup> [3248-13100]  
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]



MATERIAL

2

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127[.005]

4 PLC ± -

ANGLES ± -

FINISH

3

DWN  
LEMUEL OLMEDA  
3/10/93

CHK  
R HERSEY  
1/6/94

APVD  
M ELLIS  
1/6/94

PRODUCT SPEC  
UL 486 C

APPLICATION SPEC  
—

WEIGHT  
—

 TE Connectivity

NAME  
  
SPLICE, CLOSED-END,  
WIRE SIZE: 22-10 AWG

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C=55929

RESTRICTED TO  
—

CUSTOMER DRAWING

SCALE  
4:1

SHEET  
1 OF 1

REV  
D1

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55929-1](#)