

SPECIFICATION CONTROL DRAWING

55A1851

TITLE FIVE CONDUCTOR CABLE, RADIATION-CROSSLINKED, EXTRUDED, MODIFIED, FLUOROPOLYMER-INSULATED, SHIELDED, JACKETED, NORMAL WEIGHT, 600 VOLT

Date 4-19-91


Revision B

This specification sheet forms a part of the latest issue of Raychem Specification 55A

COMPONENT WIRES - 55A0811

SHIELD - TIN-COATED COPPER

JACKET - RADIATION-CROSSLINKED, EXTRUDED, MODIFIED FLUOROPOLYMER



FILAMENT BINDER AS REQUIRED

CABLE CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lb/1000 ft)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A1851-30-*	30	38	.006	.008	.118	.135	11.6
55A1851-28-*	28	38	.006	.008	.127	.143	13.8
55A1851-26-*	26	38	.006	.008	.140	.160	17.4
55A1851-24-*	24	38	.006	.008	.154	.175	21.4
55A1851-22-*	22	38	.006	.008	.170	.193	28.0
55A1851-20-*	20	38	.006	.008	.191	.218	37.9
55A1851-18-*	18	38	.007	.009	.223	.253	52.5
55A1851-16-*	16	38	.007	.009	.245	.279	64.1
55A1851-14-*	14	38	.007	.009	.291	.336	92.8
55A1851-12-*	12	36	.008	.010	.341	.393	133.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

FLAMMABILITY:

Procedure 1, 3 seconds (maximum); 3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lb/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100% test

LIFE CYCLE: 230 ± 3°C for 500 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST: (After Accelerated Aging, Immersion, Life Cycle and Low-Temperature-Cold Bend) 1000 volts, 60 Hz, 1 minute

PART NUMBER:

The *** in the part numbers shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, white, black, brown, red, orange and blue component wires; white jacket:

55A1851-20-9/0/1/2/3/6-9

NOTE: Nominal values are for information only.
Nominal values are not requirements.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

Raychem

Raychem Corporation
300 Constitution Drive, Menlo Park, California 94025
(415) 361 3333 TWX 910 373 1728

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[444133-000](#)