

SPECIFICATION CONTROL DRAWING

SCD

55A4831

Title

THREE CONDUCTOR CABLE, JACKETED, GENERAL PURPOSE, 600 VOLT

Date

5-7-18


Revision

C

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A0811

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE



CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
		MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A4831-28-*	28	.006	.008	.092	.097	5.9
55A4831-26-*	26	.006	.008	.102	.108	7.3
55A4831-24-*	24	.006	.008	.113	.119	9.4
55A4831-22-*	22	.006	.008	.124	.130	12.4
55A4831-20-*	20	.006	.008	.141	.148	17.4
55A4831-18-*	18	.006	.008	.167	.176	25.6
55A4831-16-*	16	.006	.008	.182	.191	31.5
55A4831-14-*	14	.007	.009	.221	.232	47.6
55A4831-12-*	12	.007	.009	.258	.271	69.0
55A4831-10-*	10	.007	.009	.307	.323	107.
55A4831-8-*	8	.009	.011	.443	.465	198.
55A4831-6-*	6	.010	.012	.545	.572	307.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

FLAMMABILITY: Procedure 1,

3 seconds (maximum), 3 inches (maximum);

no flaming or facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

1/ PART NUMBER:

The "" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

Example: AWG 24, orange, blue, and white component wires; white jacket: 55A4831-24-3/6/9-9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1

Raychem, TE Connectivity, and TE connectivity (logo) are trademarks.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-522-6752
Fax: 1-650-361-6297

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[235391-000](#)