


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		A4	REVISED PER ECR-18-014989	26SEP2018	BW	JH

D



VARNISH RESIST OVER TIN.




SLOT ACCEPTS 0.91–1.15mm [#19–#17] AWG COPPER MAGNET WIRE OR SLOT ACCEPTS 0.97–1.22mm [#18.5–#16.5] AWG ALUMINIUM MAGNET WIRE. ALUMINIUM WIRE RANGE IS APPLICABLE FOR POST TIN PLATED PARTS ONLY. 2 WIRES OF THE SAME SIZE MAX PER SLOT.



3

AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.

C



B



A

LOOSE PIECE	63643-1
TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 3/7/92	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK JEFF R. RUTH 3/9/92				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD NELSON E. NEFF 3/11/92	NAME		
	0 PLC ± -		PRODUCT SPEC	TAB, 4.75 [.187] FASTON, TM MAG-MATE TM		
	1 PLC ± -		108-2053			
	2 PLC ± 0.25 [.010]		APPLICATION SPEC			
MATERIAL BRASS		FINISH Feature 1 callout symbol	114-2066	SIZE A2	CAGE CODE 00779	DRAWING NO C-63643
CUSTOMER DRAWING			WEIGHT -	RESTRICTED TO -		SCALE 6:1
			SHEET 1 OF 1		REV A4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[63643-1](#)