






THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION 20
ALL RIGHTS RESERVED.
© COPYRIGHT 20 BY -



796739-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	C	PACKAGING CHANGED FROM BLACK POLYURETHANE SPONGE TO TRAY	12MAR2018	RK PS

NOTES:

1. MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-VO, COLOR GREEN
CLAMP: BRASS, NICKEL PLATED.
CLAMPING SCREW: M3.5, BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
2. MECHANICAL
WIRE STRIPPING LENGTH : 7.0-8.0 mm
MIN. PC BOARD HOLES DIAMETER : 1.3 mm
MAX. PC BOARD THICKNESS : 4 mm
RECOMMENDED TIGHTENING TORQUE FOR SCREW : 0.8 Nm.
3. ELECTRICAL
WIRE RANGE : 10-30 AWG
MAX. VOLTAGE : 600 V
MAX CURRENT : 30 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)
4. END-TO-END STACKABLE W/INTERLOCK, WITHOUT LOSS OF CENTERLINE SPACING.
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORY INC. FILE No. E60677.
6. NOT CUMULATIVE TOLERANCE.
7. PARTS LARGER THAN 3 POSITION ARE MADE FROM INTERLOCKING 2 OR 3 POSITION PARTS TOGETHER.
8. PACKED IN TRAY.

AR	796739-2 796739-3	95.20	10	I - 796739 - 0
2	796739-2	38.08	4	796739 - 4
-	-	28.56	3	796739 - 3
-	-	19.04	2	796739 - 2
QTY	PART NO			
MAKE FROM	7	L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 02MAR2001	CHK E. ZANOLINI 02MAR2001	APVD D. BIEVENOUR 02MAR2001	NAME TERMINAL BLOCK, PCB MOUNT SIDE WIRE ENTRY, HIGH CURRENT W/INTERLOCK, 9.52mm PITCH
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:				
mm					
0 PLC	±0.15				
1 PLC	±0.2				
2 PLC	±0.2				
3 PLC	±-				
4 PLC	±-				
ANGLES	±2				
APPLICATION SPEC					
-					
PRODUCT SPEC					
-					
MATERIAL	FINISH				
SEE NOTES	SEE NOTES				
WEIGHT	-				
CUSTOMER DRAWING					
SCALE	3:1	SHEET	1 OF	REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[796739-2](#)