


4

3


2

1





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	00		C	REVISED PER ECR-19-014502	17SEP2019	T.S	E.I



SECTION A-A





SECTION B-B



- NOTES:
- 1 FINISH : 0.2um MIN GOLD (CONTACT AREA) PLATING OVER Ni UNDER PLATING ALL OVER EXCEPT INSIDE OF CONTACT BOX GOLD PLATING THK DID NOT CONTROLL AT CONTACT TIP AREA
 - 2. TOLERANCES UNLESS OTHERWISE SPECIFIED
 - * ≤10 : ±0.3
 - 10< * ≤30 : ±0.35
 - 30< * ≤100: ±0.4
 - ANGLE: ±3°

1	84695-1
FINISH	PART NO.

WIRE RANGE	INSULATION DIA
3.08/5.5mm ² AWG #12/#10	4/5.2mmø

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WY LEE	3JAN'00	 TE Connectivity				
DIMENSIONS:		CHK LP TAN	3JAN'00	NAME TAB CONTACT "M" SIZE <DYNAMIC D-5000 SERIES>				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD WL CHOO	31MAY'01					
		PRODUCT SPEC —		SIZE A3				
		APPLICATION SPEC 114-5206						
MATERIAL COPPER ALLOY		WEIGHT 2.08g		CAGE CODE 00779		DRAWING NO C-84695		
FINISH SEE TABLE		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[84695-1](#)