




























REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W4	REVISED PER ECO-13-004115	07MAR13	KH	JO
	Y	REVISED PER ECO-18-000976	18MAY2018	RS	JO



 OBSOLETE	ALL	2	81.28	[3.200]	31	64	<del>6-87631-6</del>
	NONE	2	81.28	[3.200]	31	64	6-87631-5
 OBSOLETE	ALL	2	73.66	[2.900]	28	58	6-87631-4
	NONE	2	73.66	[2.900]	28	58	<del>6-87631-3</del>
 OBSOLETE	-	-	-	-	-	-	6-87631-2
	-	-	-	-	-	-	6-87631-1
	ALL	2	60.96	[2.400]	23	48	6-87631-0
	NONE	2	60.96	[2.400]	23	48	<del>5-87631-9</del>
 OBSOLETE	ALL	2	88.90	[3.500]	35	72	<del>5-87631-8</del>
	NONE	2	88.90	[3.500]	35	72	5-87631-7
 OBSOLETE	ALL	2	88.90	[3.500]	34	70	5-87631-6
	NONE	2	88.90	[3.500]	34	70	5-87631-5
	ALL	2	83.82	[3.300]	32	66	5-87631-4
	NONE	2	83.82	[3.300]	32	66	<del>5-87631-3</del>
 OBSOLETE	ALL	2	76.20	[3.000]	29	60	5-87631-2
	NONE	2	76.20	[3.000]	29	60	5-87631-1
	-	-	-	-	-	-	5-87631-0
	-	-	-	-	-	-	4-87631-9
 OBSOLETE	-	-	-	-	-	-	4-87631-8
	-	-	-	-	-	-	4-87631-7
	ALL	2	68.58	[2.700]	26	54	<del>4-87631-6</del>
	NONE	2	68.58	[2.700]	26	54	4-87631-5
 OBSOLETE	ALL	2	66.04	[2.600]	25	52	4-87631-4
	NONE	2	66.04	[2.600]	25	52	4-87631-3
	ALL	2	63.50	[2.500]	24	50	4-87631-2
	NONE	2	63.50	[2.500]	24	50	4-87631-1
 OBSOLETE	ALL	2	55.88	[2.200]	21	44	4-87631-0
	NONE	2	55.88	[2.200]	21	44	3-87631-9
	ALL	2	53.34	[2.100]	20	42	<del>3-87631-8</del>
	NONE	2	53.34	[2.100]	20	42	3-87631-7
 OBSOLETE	ALL	2	50.80	[2.000]	19	40	3-87631-6
	NONE	2	50.80	[2.000]	19	40	3-87631-5
	ALL	2	48.26	[1.900]	18	38	3-87631-4
	NONE	2	48.26	[1.900]	18	38	3-87631-3
 OBSOLETE	ALL	2	45.72	[1.800]	17	36	3-87631-2
	NONE	2	45.72	[1.800]	17	36	3-87631-1
	ALL	2	43.18	[1.700]	16	34	3-87631-0
	NONE	2	43.18	[1.700]	16	34	2-87631-9
 OBSOLETE	ALL	2	40.64	[1.600]	15	32	2-87631-8
	NONE	2	40.64	[1.600]	15	32	2-87631-7
	ALL	2	38.10	[1.500]	14	30	2-87631-6
	NONE	2	38.10	[1.500]	14	30	2-87631-5
 OBSOLETE	ALL	2	35.56	[1.400]	13	28	2-87631-4
	NONE	2	35.56	[1.400]	13	28	2-87631-3
	ALL	2	33.02	[1.300]	12	26	2-87631-2
	NONE	2	33.02	[1.300]	12	26	2-87631-1
 OBSOLETE	ALL	2	30.48	[1.200]	11	24	2-87631-0
	NONE	2	30.48	[1.200]	11	24	1-87631-9
	ALL	2	27.94	[1.100]	10	22	1-87631-8
	NONE	2	27.94	[1.100]	10	22	1-87631-7
 OBSOLETE	ALL	2	25.40	[1.000]	9	20	1-87631-6
	NONE	2	25.40	[1.000]	9	20	1-87631-5
	ALL	1	22.86	[.900]	8	18	1-87631-4
	NONE	1	22.86	[.900]	8	18	1-87631-3
 OBSOLETE	ALL	1	20.32	[.800]	7	16	1-87631-2
	NONE	1	20.32	[.800]	7	16	1-87631-1
	ALL	1	17.78	[.700]	6	14	1-87631-0
	NONE	1	17.78	[.700]	6	14	87631-9
 OBSOLETE	ALL	1	15.24	[.600]	5	12	87631-8
	NONE	1	15.24	[.600]	5	12	87631-7
	ALL	1	12.70	[.500]	4	10	87631-6
	NONE	1	12.70	[.500]	4	10	87631-5
 OBSOLETE	ALL	1	10.16	[.400]	3	8	87631-4
	NONE	1	10.16	[.400]	3	8	87631-3
	ALL	1	7.62	[.300]	2	6	87631-2
	NONE	1	7.62	[.300]	2	6	87631-1

MARKING		NO. OF DETENTS		D		NO. OF SPACES		NO. OF POSN		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN F. BRANDBERG		09FE994		 TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		CHK S. SHUEY		08NOV94					
		APVD D. DUPLER		08NOV94		NAME		CONNECTOR, MOD IV, CRIMP SNAP-IN, WITH DETENT			
		PRODUCT SPEC									
		APPLICATION SPEC									
MATERIAL		FINISH		WEIGHT		SIZE		CASE CODE		DRAWING NO	
						A1		00779		C-87631	
CUSTOMER DRAWING						SCALE		4:1		SHEET 1 of 1	
										REV Y	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-87631-4](#)