

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWING	09SEP2019	VM	DH

Ordering Information and Coil Characteristics — No models in this series are maintained in stock.

Type	Part Number	Contacts	Coil Voltage (60 Hz. for AC)	Coil Power* (Watts)	Breakdown (Volts RMS)
Small Non-Latching	MDR-131-1	4PDT	115 VAC	6.5	1,230
	MDR-131-2	4PDT	440 VAC	5.1	1,880
	MDR-135-1	4PDT	28 VDC	10.0	1,308
	MDR-137-8	4PDT	125 VDC	10.3	2,375
	MDR-134-1	8PDT	115 VAC	6.5	1,230
	MDR-134-2	8PDT	440 VAC	5.1	1,880
	MDR-136-1	8PDT	28 VDC	10.0	1,308
	MDR-138-8	8PDT	125 VDC	10.3	2,375
	MDR-163-1	12PDT	115 VAC	6.9	1,230
	MDR-163-2	12PDT	440 VAC	6.3	1,880
Medium Non-Latching	MDR-170-1	16PDT	115 VAC	17.0	1,230
	MDR-170-2	16PDT	440 VAC	17.0	1,880
	MDR-172-1	16PDT	28 VDC	18.7	1,308
	MDR-173-1	16PDT	125 VDC	16.0	2,375
	MDR-141-1	24PDT	115 VAC	17.0	1,230
	MDR-141-2	24PDT	440 VAC	17.0	1,880
	MDR-167-1	24PDT	28 VDC	18.7	1,308
	MDR-142-1	24PDT	125 VDC	16.0	2,375
Small Latching	MDR-67-2	4PDT	115 VAC	5.5	1,230
	MDR-4091	4PDT	440 VAC	3.0	1,880
	MDR-67-3	4PDT	28 VDC	21.8	1,308
	MDR-5060	4PDT	125 VDC	20.6	2,375
	MDR-4076	8PDT	115 VAC	5.5	1,230
	MDR-4092	8PDT	440 VAC	3.0	1,880
	MDR-5035	8PDT	28 VDC	21.8	1,308
	MDR-5061	8PDT	125 VDC	20.6	2,375
Medium Latching	MDR-6064	12PDT	115 VAC	12.0	1,230
	MDR-6065	12PDT	440 VAC	5.7	1,880
	MDR-7020	12PDT	28 VDC	8.8	1,308
	MDR-7035	12PDT	125 VDC	10.4	2,375
	MDR-66-4	16PDT	115 VAC	12.0	1,230
	MDR-6066	16PDT	440 VAC	5.7	1,880
	MDR-7025	16PDT	28 VDC	8.8	1,308
	MDR-7036	16PDT	125 VDC	10.4	2,375

Specifications

Contact Data

Arrangements — 4 Form C (4PDT) through 24 Form C (24 PDT).

Contact Ratings

Single Contacts	Two Contacts in Series
10 A, 115 VAC	3 A, 440 VAC
3 A, 28 VDC	15 A, 115 VAC
0.8 A, 125 VDC	1.5 A, 125 VDC

The above AC contact ratings are based on contact loads having a 50% power factor. The DC contact ratings are based on resistive loads.

Latching Two-Position Types —

Except for the latching feature, MDR latching relays utilize the same general construction as non-latching types. They have two sets of coils and provide a latching two-position operation.

Operate Data @ 77°F [25°C]

Type	Typ. Operate Time (ms)	Typ. Release Time (ms)
Small AC Non-Latching	5 to 12	5 to 18
Small DC Non-Latching	15 to 30	5 to 15
Small AC Latching	6 to 12	N/A
Small DC Latching	10 to 16	N/A
Medium AC Non-Latching	6 to 12	6 to 20
Medium DC Non-Latching	65 to 90	10 to 30
Medium AC Latching	50 (max.)	N/A
Medium DC Latching	30 to 80	N/A

Environmental Data

Temperature Range —

Standard models — 0°F to +149°F  
[0°C to +65°C]

Special order models — 0°F to +194°F  
[0°C to +90°C]

Mechanical Data

Termination — #5-40 screw terminals supplied

Weight (Approx.) —

Small —  
4 & 8PDT — 32 oz. [0.914 kg];  
12PDT — 33 oz. [0.943 kg]

Medium —  
16PDT — 72 oz. [2.04 kg];  
24PDT — 74 oz. [2.10 kg]

**Note:** All values are for reference, specific values may be different and subject to environmental factors such as temperature, humidity, pressure or variations in voltage.

Product Facts



- AC and DC coils, latching and non-latching
- 4PDT through 24PDT contact arrangements
- Designed to withstand high impact shock per MIL-S-901



Small 8PDT



Medium 24PDT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VM 09SEP2019		<div>TE Connectivity</div>									
		CHK RV 09SEP2019											
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD DH 09SEP2019		NAME							
				PRODUCT SPEC		MDR SERIES ROTARY RELAY  —  —							
				—									
				APPLICATION SPEC									
MATERIAL  —		FINISH  —		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
				A3		—		C=MDR—SERIES		—			
				CUSTOMER DRAWING				SCALE NTS		SHEET 1 OF 2		REV A	




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

Outline Dimensions


Tolerances: Decimals ± .010 [±.25] Unless Otherwise Specified.

Small Models




Overall Height  
4PDT 3.13 [79.5] Max.  
8PDT 3.53 [89.7] Max.  
12PDT 3.88 [98.6] Max.

Coil and Contact Terminal Screws  
#5-40 Supplied.




Medium Models




Overall Height  
12PDT 4.63 [117.6] Max.  
16PDT 5.00 [127.0] Max.  
24PDT 5.75 [146.1] Max.



Coil and Contact Terminal Screws #5-40 Supplied.



Contact Section





Contacts Shown With  
Coil 1-2 De-Energized  
and Coil 3-4 Energized.



Coils Must be Energized Alternately,  
Not Simultaneously.

ALL DIMENSIONS ARE IN INCHES (MM).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VM 09SEP2019		<div>TE Connectivity</div>				
		CHK RV 09SEP2019						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		APVD DH 09SEP2019		MDR SERIES ROTARY RELAY  —  —				
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —		FINISH —		SIZE A3	CAGE CODE —	DRAWING NO C-MDR-SERIES	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS	SHEET 2 of 2	REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MDR-163-1](#)