

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.


© COPYRIGHT 2020

TE Connectivity Ltd.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	20JAN2020	AFK	LS


FLATTENED WIDTH




D

d


w



EXPANDED TUBING PRODUCT



SPOOL



SPOOL I.D.

101 (4.0)

Product Size	2.4	3.2	4.8	6.4	9.5	12	18	25	38
"D" Minimum Supplied I.D.	2.4 (.094)	3.2 (.126)	4.8 (.189)	6.4 (.252)	9.5 (.374)	12.7 (.500)	19.1 (.752)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	0.8 (.031)	1.1 (.043)	1.6 (.063)	2.1 (.083)	3.2 (.126)	4.2 (.165)	6.4 (.252)	8.5 (.335)	19.1 (.752)
"w" Recovered Wall Thickness ±0.08 (.003)	0.51 (.020)	0.51 (.020)	0.58 (.023)	0.58 (.023)	0.61 (.024)	0.61 (.024)	0.61 (.024)	0.64 (.025)	0.64 (.025)
Minimum Sleeve Flattened Width	4.30 (.169)	5.82 (.229)	8.00 (.315)	10.65 (.419)	15.5 (.610)	20.4 (.803)	30.5 (1.201)	40.4 (1.591)	60.3 (2.374)


NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL

CROSSLINKED POLYOLEFIN

DWN AFK 09JAN2020

CHK -


APVD LS 20JAN2020

PRODUCT SPEC RW-2519

APPLICATION SPEC -

WEIGHT VARIOUS

CUSTOMER DRAWING

TE Connectivity

NAME

D-CT

OUTSIDE PRINTER SPOOL

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A30198G

C-MCD170014

-

SCALE -

SHEET 1 OF 1

REV 2

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8087-000](#)