


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18JAN2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X



-	-	CABLE	6
-	-	LABEL	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM





TABLE 1		
TECHNICAL DATA	T40512X0003-00X	T40512X0004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

WIRES: 0.25mm ² (24AWG)	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -**0:**.0m -**1:**.5m	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-MR-4CON-PUR-**5	4	T4051220004-00X		
					RPC-M8-MR-3CON-PUR-**5	3	T4051220003-00X		
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-MR-4CON-PVC-**5	4	T4051210004-00X		
					RPC-M8-MR-3CON-PVC-**5	3	T4051210003-00X		
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm  MATERIAL TBD		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± 4 PLC ± ANGLES ± - FINISH -		DWN Nick Pan 02DEC2015	TE Connectivity M8 CABLE RIGHT ANGLE SINGLE ENDED MALE SIDE, UNSHIELDED				
		CHK Kobby Zhao 02DEC2015		NAME					
		APVD Xiang Xu 02DEC2015							
		PRODUCT SPEC 108-106140							
		APPLICATION SPEC -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT -		A2	-	G- T40512X000X00X	-		
CUSTOMER DRAWING				SCALE	2:1	SHEET	1 OF 1	REV	A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4051210004-001](#)