




NOTES:

1. TECHNICAL DATA: SEE TABLE 1
2. RECOMMEND TORQUE 0.4Nm
3. TE LABLE AREA.
4. - ** : CABLE LENGHT. -0.5:0.5m, -1.0:1.0m, -1.5:1.5m...
5. INSERT MARK FOR MATING.
6. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

注意事项

1. 技术参数：见表1
2. 推荐扭矩0.4Nm；
3. TE 标签位置；
4. - ** 线长：-0.5:0.5m, -1.0:1.0m, -1.5:1.5m
5. 产品对插标示；
6. 产品必须符合ROHS与REACH.

TABLE 1

TECHNICAL DATA	T40522X4003-00X	T40522X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

		TE LABLE	10
		CABLE	9
	COPPER ALLOY	NUT	8
	RUBBER	O-RING	7
	PA66	HOUSING	6
	COPPER ALLOY	CONTACT	5
	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	-001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-**-M8-4FR-PUR 4 4 T4052224004-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-3MR-**-M8-3FR-PUR 4 3 T4052224003-00X
					RPC-M8-4MR-**-M8-4FR-PVC 4 4 T4052214004-00X
					RPC-M8-3MR-**-M8-3FR-PVC 4 3 T4052214003-00X
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE POS. PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.					DWN Nick Pan 25FEB2016
DIMENSIONS: mm					CHK Kobby Zhao 25FEB2016
TOLERANCES UNLESS OTHERWISE SPECIFIED:					APVD Xiang Xu 25FEB2016
0 PLC ±- 1 PLC ±0.50 2 PLC ±0.35 3 PLC ± 4 PLC ± ANGLES ± FINISH -					PRODUCT SPEC 108-106140
MATERIAL TBD material_2					APPLICATION SPEC -
					WEIGHT -
CUSTOMER DRAWING					NAME M8 CABLE ASSEMBLY UNSHIELDED DOUBLE ENDED TYPE
					SIZE A2
					CAGE CODE -
					DRAWING NO. C-T40522X400X00X
					RESTRICTED TO -
					SCALE 1:1
					SHEET 1 OF 1
					REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052214004-004](#)