

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

0m TO 1m: ±0.05m
1m TO 3m: ±0.10m
>3m: ±1.5%

28.8±0.5

50REF.

35±5

26.7REF.

2

3

4

5

6

7

1

3pos

4POS.

PIN4 BLACK

PIN3 BLUE

PIN1 BROWN

PIN2 WHITE

PIN1 BROWN

VIEW A 3POS.

VIEW A 4POS.

TE

VIEW A

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02MAR2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X

NOTES:

1. TECHNICAL DATA: SEE TABLE 1

2. STRIP AND RETAIN THE INSULATION

3. RECOMMEND TORQUE 0.4Nm

4. TE LABEL AREA.

5. -*: CABLE LENGHT.-0.5:0.5m, -1.0:1.0m, -1.5:1.5m...

6. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

注意事项

1. 技术参数：见表1

2. 剥线并保留绝缘层；

3. 推荐扭矩0.4Nm；

4. TE 标签位置；

5. -**线长：-0.5:0.5m, -1.0:1.0m, -1.5:1.5m

6. 产品必须符合ROHS与REACH.

-	BRASS	SHIELDING	7
-	-	CABLE	6
-	-	LABLE	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -**: 00.0m -001: **.5m	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-MR-4CON-PUR-**SH	4	T4061220004-00X
					RPC-M8-MR-3CON-PUR-**SH	3	T4061220003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-MR-4CON-PVC-**SH	4	T4061210004-00X
					RPC-M8-MR-3CON-PVC-**SH	3	T4061210003-00X
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

TBD

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.50
2 PLC ±0.35
3 PLC ±
4 PLC ±
ANGLES ±-
FINISH -
-

DWN

28JAN2016

Nick Pan

CHK

28JAN2016

Kobby Zhao

APVD

28JAN2016

Xiang Xu

PRODUCT SPEC

108-106140

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

M8 CABLE ASSEMBLY SHIELDED RIGHT ANGLE, MALE, SINGLE END TYPE

NAME

-

SIZE

A2

CAGE CODE

-

DRAWING NO

©T40612X000X00X

RESTRICTED TO

-

SCALE

1:1

SHEET

1

OF

1

REV

A1

TABLE 1

TECHNICAL DATA	T40612X0003-00X	T40612X0004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4061210003-002](#)