

REV. 0

DCO 143667

COIL: @ 25°C

RESISTANCE 880 OHMS ±10%

NOMINAL VOLTAGE 18.0 VDC

MUST OPERATE 11.5 VDC

MUST RELEASE 7.3 VDC MAX. 1.4 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 4.0 MS MAX

CONTACT STABILIZATION 2.5 MS MAX.

## CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB '7 OCT 02

CR. *[Signature]* 10/7/02

**CII Technologies**  
advanced control electronic solutions

CUST. QPL

CUST. NO. M39016/19-029M

REV.

"JMGADD" RELAY

JMGAPDD-18M

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1617571-4](#)