

REV. 0
DCO 143670

COIL: @ 25°C

RESISTANCE 125 OHMS \pm 10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.8 VDC

MUST RELEASE 1.7 VDC MAX., 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.

RELEASE TIME 7.5 MS MAX.

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 14OCT02

CK *[Signature]* 10/19/02

CII Technologies
advanced control electronic solutions

CUST. CII

CUST. NO. STANDARD

REV.

"PR1MSD" RELAY

PR1MSPD-5X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1617598-7](#)