




SECTION J - J

1. COPPER ALLOY C97
2. 1.27µm MIN GOLD PER ASTM B488 OVER 2.54µm
MIN NICKEL PER QQ-N-290 ON ENTIRE STOCK.
3. OPTIONAL ALTERNATE MARKING: LETTER "S"
4. BLUE COLOR BAND
5. APPLICABLE WIRE SIZE: 16-18-20 AWG
WIRE INSULATION DIAMETER: 2.6 mm MAX
INSULATION STRIP LENGTH: 6.0-6.5mm
6. APPLICATION TOOLING:
CRIMPING TOOL: TYCO PART NUMBER 601967-1 (M22520/1-01)
POSITIONER: TYCO PART NUMBER 601967-2 (M22520/1-02)
SELECTOR POSITION: AWG 16: 6
AWG 18: 5
AWG 20: 4
CONTACT INSERTION/EXTRACTION TOOL: 91066-3 (M81969/1-03)

7. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TWO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 250CT2005 BH CHR 250CT2005 JPM APVD 250CT2005		tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608		NUMBER	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±0.1 2 PLC ±0.05 3 PLC ±.1 4 PLC ±.1 ANGLES ±1 FINISH		NAME PIN CONTACT, SIZE 16, GPR - -		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL 		WEIGHT -		A200779		C-1738013	
		CUSTOMER DRAWING		SCALE 20:1		SHEET OF REV	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738013-1](#)