




LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			K		EC 0G3C 0216 05		27 DEC 05	BSV	JLG
			K1		REVISED PER ECO-09-020774		22AUG09	KK	AEG

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING.
- 3 .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 4 .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



5	OBSOLETE	4	2.570	2.400	24	50	7-102318-5
5	OBSOLETE	4	1.570	1.400	14	30	6-102318-6
5	OBSOLETE	4	1.070	.900	9	20	6-102318-1
	OBSOLETE	3	3.270	3.100	31	64	3-102318-1
	OBSOLETE	3	3.170	3.000	30	62	3-102318-0
	OBSOLETE	3	2.970	2.800	28	58	2-102318-9
	OBSOLETE	3	2.870	2.700	27	56	2-102318-8
	OBSOLETE	3	2.770	2.600	26	54	2-102318-7
	OBSOLETE	3	2.670	2.500	25	52	2-102318-6
5	OBSOLETE	3	2.570	2.400	24	50	2-102318-5
	OBSOLETE	3	2.470	2.300	23	48	2-102318-4
	OBSOLETE	3	2.370	2.200	22	46	2-102318-3
	OBSOLETE	3	2.270	2.100	21	44	2-102318-2
	OBSOLETE	3	2.170	2.000	20	42	2-102318-1
	OBSOLETE	3	2.070	1.900	19	40	2-102318-0
	OBSOLETE	3	1.970	1.800	18	38	1-102318-9
	OBSOLETE	3	1.870	1.700	17	36	1-102318-8
	OBSOLETE	3	1.770	1.600	16	34	1-102318-7
		3	1.570	1.400	14	30	1-102318-6
	OBSOLETE	3	1.470	1.300	13	28	1-102318-5
	OBSOLETE	3	1.370	1.200	12	26	1-102318-4
	OBSOLETE	3	1.270	1.100	11	24	1-102318-3
	OBSOLETE	3	1.170	1.000	10	22	1-102318-2
		3	1.070	.900	9	20	1-102318-1
	OBSOLETE	3	.970	.800	8	18	1-102318-0
	OBSOLETE	3	.870	.700	7	16	102318-9
	OBSOLETE	3	.770	.600	6	14	102318-8
	OBSOLETE	3	.670	.500	5	12	102318-7
	OBSOLETE	3	.570	.400	4	10	102318-6
	OBSOLETE	3	.470	.300	3	8	102318-5
	OBSOLETE	3	.370	.200	2	6	102318-4
	OBSOLETE	3	3.070	2.900	29	60	102318-3
	OBSOLETE	3	.270	.100	1	4	102318-2
	OBSOLETE	3	1.670	1.500	15	32	102318-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL: HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK, POSTS-PHOS. BRONZE

FINISH: SEE TABLE

DWN: H MOLL 11-16-87

CHK: R FEIDT 11-16-87

APVD: R FEIDT 11-16-87

PRODUCT SPEC: ---

APPLICATION SPEC: ---

WEIGHT: ---

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME: ---

SIZE: ---

CAGE CODE: ---

DRAWING NO: 100779

RESTRICTED TO: ---

PLATING: C

B

A

NO OF POSN: ---

PART NUMBER: ---

SCALE: 4:1

SHEET: 1 OF 1

REV: K1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-102318-6](#)