



## MODEL 44906

### GSFC Space Qualified Thermistor

- Fully Qualified to GSFC S311-P18-06S7R6 Specification for Flight Use
- 5000 ohm Resistance @ 25°C
- Interchangeable  $\pm 0.1^{\circ}\text{C}$ , 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- Thermally conductive epoxy coating that meet Outgassing Requirements
- 32 AWG, 3" (7.6 cm) long Solder plated copper leads
- Serialized and Color Coded for Identification

### FEATURES

- Flight Qualified
- 5000 ohm Resistance @ 25°C
- Interchangeability
- High Sensitivity
- Thermally Conductive Epoxy Coating  
Exhibits <0.66% TML, <0.01% CVCM, 0.10% WVR when tested per ASTM E-595-90

### APPLICATIONS


- Extended Space Applications
- Low and Mid Range Temperature Applications
- Tight Tolerance Instrumentation
- Applications Requiring Sensing Small Changes in Temperature
- Applications with Outgassing Requirements

NASA Qualified epoxy encapsulated precision interchangeable NTC thermistors for use in extended space flight applications. All parts are fully flight tested and characterized. Line re-qualified yearly per MIL-PRF-23648 requirements as specified in S311-P18 document. Resistance (Type 06) available in other lead and resistance configurations per S311-P18.

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C	Ohms	5000
Tolerance 0°C to 70°C	°C	± 0.1
Beta Value 25/85	K	3987
Tolerance on Beta Value	%	0.4
Time response in air	Seconds	< 10
Dissipation Constant in air	mW/°C	1
Insulation Resistance (Min. of 100 Mohms for 1 sec.)	Volts	500

MECHANICAL DETAILS



## TYPICAL PERFORMANCE CURVES (RESISTANCE OF INDIVIDUAL THERMISTORS)

Temp °C	K-Ohms
-55	482.2
-54	447.9
-53	416.3
-52	387.1
-51	360.2
-50	335.3
-49	312.3
-48	291.0
-47	271.3
-46	253.0
-45	236.2
-44	220.5
-43	205.9
-42	192.5
-41	180.0
-40	168.3
-39	157.5
-38	147.5
-37	138.2
-36	129.5
-35	121.4
-34	113.9
-33	106.9
-32	100.3
-31	94.22
-30	88.53
-29	83.22
-28	78.26
-27	73.62
-26	69.29
-25	65.24
-24	61.45
-23	57.90
-22	54.58
-21	51.47
-20	48.56
-19	45.83
-18	43.27
-17	40.86
-16	38.61

Temp °C	K-Ohms
-15	36.49
-14	34.50
-13	32.63
-12	30.88
-11	29.23
-10	27.67
-9	26.21
-8	24.83
-7	23.54
-6	22.32
-5	21.17
-4	20.08
-3	19.06
-2	18.10
-1	17.19
0	16.33
1	15.52
2	14.75
3	14.03
4	13.34
5	12.70
6	12.09
7	11.51
8	10.96
9	10.44
10	9.951
11	9.486
12	9.046
13	8.628
14	8.232
15	7.857
16	7.500
17	7.162
18	6.841
19	6.536
20	6.247
21	5.972
22	5.710
23	5.462
24	5.225

Temp °C	K-Ohms
25	5.000
26	4.787
27	4.583
28	4.389
29	4.204
30	4.029
31	3.861
32	3.702
33	3.549
34	3.404
35	3.266
36	3.134
37	3.008
38	2.888
39	2.773
40	2.663
41	2.559
42	2.459
43	2.363
44	2.272
45	2.184
46	2.101
47	2.021
48	1.944
49	1.871
50	1.801
51	1.734
52	1.670
53	1.608
54	1.549
55	1.493
56	1.439
57	1.387
58	1.337
59	1.290
60	1.244
61	1.200
62	1.158
63	1.117
64	1.079

Temp °C	K-Ohms
65	1.041
66	1.006
67	0.9711
68	0.9380
69	0.9063
70	0.8757

## MODEL 44906

GSFC Space Qualified Thermistor

### ORDERING INFORMATION

Part Number	Description	$\Omega$ @25°C
095805	44906 THERM GSFC 311P18-06S7R6	5,000
SP44906X-xx	44906X GSFC 311P18-06, Various Lead lengths and Types	5,000

#### NORTH AMERICA

Measurement Specialties, Inc.,  
a TE Connectivity Company  
Tel: 800-522-6752  
[customercare.ando@te.com](mailto:customercare.ando@te.com)

#### EUROPE

Measurement Specialties (Europe), Ltd.,  
a TE Connectivity Company  
Tel: 800-440-5100  
[customercare.tlse@te.com](mailto:customercare.tlse@te.com)

#### ASIA

Measurement Specialties (China), Ltd.,  
a TE Connectivity Company  
Tel: 0400-820-6015  
[customercare.chdu@te.com](mailto:customercare.chdu@te.com)

#### [te.com/sensorsolutions](http://te.com/sensorsolutions)

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[311P18-06S7R6](#)