














- | | | | |
|---|---|--|--|
| | <p>PN 1-6</p>  <p>SCALE 1:2</p> | <p>PN 0-1</p>  <p>SCALE 1:2</p> | <p>PN 2-0</p>  <p>SCALE 1:2</p> |
| <p>PN 1-7</p>  <p>SCALE 1:2</p> | <p>PN 1-1</p>  <p>SCALE 1:2</p> | <p>PN 3-7 & 2-7</p>  <p>SCALE 1:2</p> | <p>PN 1-3 & 2-3</p>  <p>SCALE 1:2</p> |

[illegible]

TEC 07-09-001-1 IS CONTROLLED DOCUMENT FOR THIS APPLICATION. INFORMATION SHOULD BE CONTACTED FOR THE LATEST REVISIONS.				DWG Schneider 31.03.1999				TE Connectivity	
				CHK Schweizer 31.03.1999					
DIMENSIONS IN mm		TOLERANCES UNLESS SPECIFIED:		RFWD -		NAME		Hood	
		FRACTIONAL DECIMAL PLUS MINUS		PRODUCT SPEC 108-74.001				HB.16.STS.1.21.G	
0 P.L.C ±				108-74.003					
1 P.L.C ±				APPLICATION SPEC 114-74.001					
2 P.L.C ±				114-74.004					
3 P.L.C ±						SIZE CAGE CODE DRAWING NO		RESTRICTED TO	
4 ANGLES ±									
MATERIAL		FINISH		WEIGHT		A 00779 C=1102292		-	
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1102292-1](#)