

4

THIS DRAWING IS UNPUBLISHED.

3

2

1

© COPYRIGHT 2000

ALL RIGHTS RESERVED.


LOC
B1

DIST


REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ECR-15-007353	01JUN2015	GSK	JB

CONTACT ARRANGEMENT VIEW FROM CONNECTING SIDE




CONTACT ARRANGEMENT VIEW FROM TERMINATION SIDE





SCALE 1:1



NOTES

1

SUITABLE CRIMP CONTACTS: SERIES HN.D
CUSTOMER DRAWING: 1105050
OUTER DIMENSIONS OF INSULATION: MAX. Ø4mm

2

SUITABLE CONTACTS: SERIES HF.06
CUSTOMER DRAWING: 1110948
OUTER DIMENSIONS OF INSULATION: MAX. Ø15mm

3

SUITABLE CRIMP BARRELS: SERIES HF.06/08
CUSTOMER DRAWING: 1108807

4

SUITABLE MODULE FIXING FRAME: SERIES HVS SIZE 3 TO 8
CUSTOMER DRAWING: 1103250

5

SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855

6

SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855

7

STANDARDS:
DIN EN 61984; DIN EN 60664-1

8

POLARIZATION RIBS

9

MARKING OF POLARIZATION ACCORDING TO MARKING OF
MODULE FRAME

10

PACKAGING:
10 PIECES IN A CARTON

PN 0-1 AS SHOWN

1		11	12		
QTY	DESCRIPTION	MATERIAL	COLOR	NOTE	ITEM NO
	FEMALE INSERT	PBT-GF10	LIGHT GREY	HVS-HF.06.Sti	1
	HVS-HF.06.2+8.Sti.C				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
11

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±

12

DWN
SCHNEIDER
CHK
H.BRAUN
APVD
T.SCHNURPFIL

14.02.2006
14.02.2006
14.02.2006

PRODUCT SPEC
108-74024
APPLICATION SPEC
114-74077
WEIGHT

TE Connectivity

MALE INSERT
HVS-HF.06.2+8.STI.C

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1103242

RESTRICTED TO

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV D

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1103242-1](#)