

©

TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	10	INITIAL RELEASE	11FEB2020	GK	AK

NOTES: —

1. CHARACTERS: —
0–9, A–Z, +, –, /,~, ≡
0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
HEIGHT 2.6 – 2.9 mm
TOLERANCE (AXIAL) ±0.75
(ROTATIONAL) ±5°
CHEVRON CUT MARKERS: —
CHARACTERS TO BE CENTRALLY DISPOSED
ON MARKER FACE AND IN THE ATTITUDE
SHOWN RELATIVE TO CHEVRON.

2. MARKER LENGTHS (DIMENSION 'A'): —
WITH SINGLE MARK 4.00 – 4.75
WITH DOUBLE MARK 6.75 – 7.25

DIM 'A'

140°

A

CHEVRON CUT

0.95

4.85

C

STRAIGHT CUT

DIM 'A'

A

C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V	STE TE Connectivity			
		CHK 11FEB2020 ALAN KEAN				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.2 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD 11FEB2020 ALAN KEAN	NAME			
		PRODUCT SPEC	MARKER Z TYPE SIZE 11 STRAIGHT / CHEVRON CUT			
MATERIAL PVC 3.1 – 2.8g/250mm		FINISH	—	APPLICATION SPEC	—	
		—	—	WEIGHT	—	

CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-1601A0004	RESTRICTED TO
		SCALE 10:1	SHEET 1 OF 1	REV 10	

1470–19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EJ0339-000](#)